

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0433751001](#)  
**Status:** **Active**  
**Overview:** Sabre™ Power Connector  
**Description:** Sabre™ Crimp Terminal, Female, Double 18 AWG, 4.57mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact with TPA

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-44441-9999 \(PDF\)](#) [Product Literature \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	43375
Application	Power
Comments	For double crimping of 18 AWG wire in a side-by-side orientation. Terminal mates to 3.18mm wide x 0.51mm ) thick flat blade PC tab. Allows 44441 receptacle housings to comply with the UL1977 finger proof access requirement
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	<a href="#">Sabre™ Power Connector</a>
Product Literature Order No	987650-5662
Product Name	Sabre™
UPC	800754365994

**Physical**

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.360/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.57mm max.
Wire Size AWG	14, 16, 18+18
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-44441-9999, RPSX-44441-001
Sales Drawing	SD-43375-1001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contains SVHC(2015 June 15): No

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

**China RoHS**  
Green Image  
Not Relevant

**Search Parts in this Series**

[43375](#) Series

**Mates With**

[43178](#) Male Crimp Terminals

**Use With**

[44441](#) Receptacle Housings

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Extraction Tool	<a href="#">0638132700</a>
Hand Crimp Tool for Flat Blade Crimp Terminal	<a href="#">0638117300</a>

Terminator Die - Doubles	<u>0638405200</u>
Mini-Mac™ Applicator, For Narrow Insulation Crimp	<u>0638917000</u>
Mini-Mac™ Applicator	<u>0638916100</u>

This document was generated on 11/04/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**