



## Two-Piece - Inner sleeve

**T&B Catalog Number:**

GSB071

**UPC Number:**

78621081279

**Status:**

Active

**Description:**

Two Piece Inner Sleeve Connector for Hexagonal Range, Length 7.9mm, Inner Diameter 1.87mm, Outer Diameter 2.44mm, Color Green, Hard Bronze, Tin Plated

### Features

Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Hexagonal Range (the corresponding outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.

### General

Material	Hard bronze
Finish	Tin plated (per MIL-T-10727A)
Color	Green

### Dimension Information

Length (inches)	.311
Length (mm)	7.9
Inner Diameter (inches)	.071
Inner Diameter (mm)	1.87
Outer Diameter (inches)	.096
Outer Diameter (mm)	2.44

### Specifications

MIL Specification	21981-071
-------------------	-----------

### Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

### Application Support

T&B Sales Drawings	wsd-000206
Overview	Available on Website
Installation Overview	Available on Website

### Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321

