

NEW!

HDT Series Micro Mini Surface Mount Detect Switches

Features/Benefits

- Low profile package sits just 3,35 mm off PCB
- Design allows top or side actuation
- Low actuation force, 35 grams max.
- Pick and place compatible, available in tape & reel packaging
- RoHS compliant and compatible

Typical Applications

- Consumer electronics
- Computers
- Medical devices



Specifications

CONTACT RATING: 1 mA 5 VDC
 MECHANICAL AND ELECTRICAL LIFE: 100,000 cycles min.
 CONTACT RESISTANCE: 500 m Ω max. initial.
 INSULATION RESISTANCE: 100 M Ω min. between adjacent contacts.
 OPERATING TEMPERATURE: -15°C to +70°C
 STORAGE TEMPERATURE: -20°C to +75°C
 PACKAGING: Tape & reel, 2,450 per reel.
 TRAVEL:
 Pre-travel .30 mm
 Overtravel: .75 mm
 Total: 1.05 mm

Materials

BASE: PA 46
 COVER: PA 46
 ACTUATOR: PA 46
 MOVABLE BLADE: Phosphor bronze, silver plated.
 TERMINALS: Phosphor bronze, silver plated.

NOTE: For the latest information regarding RoHS compliance, please go to: www.ittcannon.com/rohs.



NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

Build-A-Switch



Complete part numbers for HDT Series are shown below.

PART NUMBER	PACKAGING	SCHEMATIC
HDT0001	TAPE & REEL	



NOTE: Available with no locating posts by adding "N" (HDT0001NP) to Part Number.



HDT0001



TAPE & REEL



Dimensions are shown: Inches (mm)
 Specifications and dimensions subject to change



Detect