

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0395021004](#)
Status: **Active**
Overview: Eurostyle™ Terminal Blocks
Description: 3.50mm Pitch Eurostyle™ Horizontal PCB Header, 4 Circuits

Documents:

[3D Model](#) [Product Specification PS-39500-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|----------------|----------------------------|
| Product Family | Terminal Blocks |
| Series | 39502 |
| Application | N/A |
| Component Type | PCB Header |
| Overview | Eurostyle™ Terminal Blocks |
| Product Name | ESE, Eurostyle™ Pluggable |
| Type | Euro Block |
| UPC | 822350434775 |

Physical

| | |
|-------------------------------|-----------------|
| Circuits (Loaded) | 4 |
| Entry Angle | N/A |
| Lock to Mating Part | None |
| Net Weight | 0.900/g |
| Number of Rows | 1 |
| Orientation | Horizontal |
| PC Tail Length | 3.50mm |
| PCB Thickness - Recommended | 2.50mm |
| Panel Mount | No |
| Pitch - Mating Interface | 3.50mm |
| Pitch - Termination Interface | 3.50mm |
| Polarized to Mating Part | Yes |
| Shrouded | Fully |
| Stackable | No |
| Temperature Range - Operating | -40°C to +105°C |
| Wire Size AWG | N/A |


Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 8.0A |
| Voltage - Maximum | 300V |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|----------------------------|
| Product Specification | PS-39500-001 |
| Sales Drawing | SD-39501-002, SD-39502-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): Yes

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

China RoHS

Green Image

Not Relevant

Search Parts in this Series

[39502](#) Series

Mates With

Most 3.50mm Pitch Industry Standard Plugs, [39500](#) Horizontal Plug, [39503](#) Vertical Plug