

PS1-3-1-65

ABB contact for United States of America



General Information

Extended Product Type:	PS1-3-1-65
Product ID:	1SAM201906R1113
EAN:	4013614400735
Catalog Description:	PS1-3-1-65 Busbar
Long Description:	PS1-3-1-65 3-phase busbar for 3 MS116 / MS132 with 1 HK/SK, Ie=65A

Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

Ordering

EAN:	4013614400735
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369010

Container Information

Package Level 1 Width:	80 mm
Package Level 1 Length:	181 mm
Package Level 1 Height:	46 mm
Package Level 1 Gross Weight:	0.638 kg
Package Level 1 EAN:	4013614488115
Package Level 1 Units:	10 piece

Dimensions

Product Net Width:	149.5 mm
Product Net Height:	32.3 mm
Product Net Depth:	13 mm
Product Net Weight:	0.06 kg

Technical

Rated Operational Voltage:	690 V
Rated Operational Current (I_e):	65 A
Degree of Protection:	IP20
Standards:	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1
Product Name:	Busbar
Suitable For:	MS116 MS132
Suitable for Product Class:	Manual Motor Starter

Environmental

Ambient Air Temperature:	Operation -25 +70 °C Storage -50 ...+80 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Ampere Rating UL/CSA:	65 A

Certificates and Declarations (Document Number)

cUL Certificate:	1SAA963001-1701
Declaration of Conformity - CE:	1SAD938509-0056
GOST Certificate:	1SAA937000-2703
RoHS Information:	1SAA963003-4402
UL Certificate:	1SAA963001-1602

Classifications

eClass:	7.0 27379201
E-nummer:	3111680
Object Classification Code:	W
UNSPSC:	39121100

