



## Smart Wifi HD Indoor Pan Tilt Zoom Camera

# SHC200

- Pan (270°), Tilt (90°) movement controlled via Smartphone or Tablet
- 10m Smart IR Night Vision
- 2.8mm Wide Angle Lens (75° Viewing Angle)
- WiFi or Wired Connection
- Email & Push notifications of all events sent directly to your PC or Smartphone/Tablet
- P2P Technology for quick, seamless Network Connectivity
- 2-way Audio
- Support up to 32GB Micro SD Card



**HD 720P  
Resolution**



**Pan Tilt Zoom**



**Wireless  
Connectivity**



**10m IR night  
Vision**

# FEATURES

Smart WiFi HD Indoor Pan Tilt Camera can be used with the Smart home system or as a standalone internal camera connected directly to the internet router using simple P2P technology, allowing remote viewing anywhere via IOS or Android OS. The Camera can be moved and zoomed in or out to get the exact image you need to see by the use of your smartphone or tablet. It has a huge number of application allow monitoring of Homes, Offices, shops etc. The camera can even be used to watch the baby up stairs while you take 5 minutes out to catch up on TV.

The SHC200 provides a High Definition 720P image, True Day Night operation with 10m Smart IR Night Vision. In addition, the camera has a 2.8mm Wide Angle Lens and can be connected by either Wi Fi or Wired Connection.

The SHC200 supports two-way audio facility by a built-in speaker and microphone to allow voice communication over the internet. The SHC200 comes with a Micro SD card slot that will support up to a 32GB memory card for 1760 motion triggered events which can be overwritten for local (Edge) recording .

## SHC200 Technical Specification

SHC200	
Brand	Smart-I
Model Number	SHC200
Style	2.8mm (75°)
Night Vision	5-10m IR Night Vision
Min. Illumination	0 Lux (IR On)
Resolution	HD 720P
Weather Resistant	No
Vandal Resistant	No
Compression	H264
Recording Modes	Motion Detection, Manual
Network Connection	WiFi (IEEE 802.11 b/g/n)
Network Protocols	TCP/IP, UDP, SMTP, NTP, DHCP, ARP
Alarm Functions	PIR, Motion Detection
Audio	2-way Audio
Operating Voltage	DC 5V 1.5A
Operating Temp.	-10°C ~ 50°C
Dimensions (WxHxD)	93x114x93mm

All specifications shown are subject to change without notice, please confirm up to date details when ordering. All network specifications and recording times are based upon theoretical scenarios.

Actual performances will vary depending on external factors. No liability will be accepted by Y3K for any errors or omissions in this information. All relevant trade marks acknowledged.  
© Y3K (Europe) Limited 2015

■ DISTRIBUTED BY

