

Extra Low Profile Xenon Strobe


This one piece, super low profile xenon strobe is part of Lynteck's commitment to continual product development. This unit is designed for use in the 12v security market.

Specification

Voltage	12Vdc
Current	160mA
Power Output	1 Watt
Flasher	Xenon
Flash Rate	100 per minute
Height	27mm
Diameter Base	68mm
Diameter Lens	65mm
Fixing	Surface mount / single fixing
Connecting Leads	Rear entry

Order Numbers

LY01-015-11	Amber
LY01-016-12	Blue
LY01-017-13	Clear
LY01-018-14	Red