

Renewal Parts

For Catalog Numbers A10, A11, A13, A30, A31, A40, A41, A50, A51, A70, A71, A80, A81, B10, B11, B50, B51, B52, C10, C30 and C50 Contactors and Starters

Note: For a complete listing of parts refer to the Renewal Parts Publication Number referenced on the device nameplate.

33

Table 33-357. Citation Renewal Parts

Description	Size 00					Size 0	
	Series A1 ①	Series B1	Series C1	Series D1/C2	Price U.S. \$	Part Number	Price U.S. \$
	Part Number	Part Number	Part Number	Part Number			

Set of Contacts

Part Number on Contactor or Starter Nameplate	Series A1 ①	Series B1	Series C1	Series D1/C2	Price U.S. \$	Size 0 Part Number	Price U.S. \$
2-Pole without Interlock	6-21	②	②	②		6-22	
3-Pole without Interlock	6-21-2	②	②	②		6-22-2	
3-Pole with Interlock	6-21-3	②	②	②		—	
4-Pole without Interlock	—	—	—	—		6-22-3	
5-Pole without Interlock	—	—	—	—		6-22-4	

Magnet Coils

Coil Suffix

	Coil Suffix	Series A1 ①	Series B1	Series C1	Series D1/C2	Price U.S. \$	Size 0 Part Number	Price U.S. \$
120V 60 Hz or 110V 50 Hz	A	9-1945-1	④	9-2650-1	9-2823-1		9-1887-1	
240V 60 Hz or 220V 50 Hz	B	9-1945-2	④	9-2650-2	9-2823-2		9-1887-2	
480V 60 Hz or 440V 50 Hz	C	9-1945-3	④	9-2650-3	9-2823-3		9-1887-3	
600V 60 Hz or 550V 50 Hz	D	9-1945-4	④	9-2650-4	9-2823-4		9-1887-4	
208V 60 Hz	E	9-1945-5	④	9-2650-5	9-2823-5		9-1887-5	
24V 60 Hz	T	9-1945-8	④	9-2650-7	9-2823-7		9-1887-7	
380V 50 Hz	L	9-1945-6	④	9-2650-6	9-2421-18 ③		9-1887-8	
120/240V 60 Hz or 110/220V 50 Hz	F	—	—	—	—		9-1888-1	
240/480V 60 Hz or 220/440V 50 Hz	G	—	—	—	—		9-1888-2	
277V 60 Hz	H	9-1945-16	④	9-2650-13	9-2823-12		9-1887-16	
208/240V 60 Hz	J	—	—	—	9-2823-17		—	
120V DC	A1	—	—	—	—		9-2024-2	
240V DC	B1	—	—	—	—		9-2024-1	
24V DC	T1	—	—	—	—		9-2024-4	
48V DC	W1	—	—	—	—		9-2024-3	

Replacement Thermal Elements

Description	Series A1 ①	Series B1	Series C1	Series D1/C2	Price U.S. \$	Size 0 Part Number	Price U.S. \$
Standard Trip Eutectic (12 teeth)	10-4767	10-4767	10-4767	10-4767		10-4767	
Slow Trip Eutectic (24 teeth)	10-5018	10-5018	10-5018	10-5018		10-5018	
Current Transformer	—	—	—	—		—	

- ① For non-reversing contactors and starters only. For Size 00 reversing, select parts from adjoining size 0 column.
- ② Replace complete contactor.
- ③ Non-encapsulated coil.
- ④ Obsolete.

Discount Symbol **1CD1C**

Table 33-357. Citation Renewal Parts (Continued)

Description	Size 1		Size 2				Size 3			
	Part Number	Price U.S. \$	Series A1		Series B1		Series A1		Series B1	
			Part Number	Price U.S. \$	Part Number	Price U.S. \$	Part Number	Price U.S. \$	Part Number	Price U.S. \$

Set of Contacts

Part Number on Contactor or Starter Nameplate										
2-Pole without Interlock	6-23		6-24		6-34		6-25		6-35	
3-Pole without Interlock	6-23-2		6-24-2		6-34-2		6-25-2		6-35-2	
3-Pole with Interlock	—		—		—		—		—	
4-Pole without Interlock	6-23-3		—		6-34-3		—		—	
5-Pole without Interlock	6-23-4		—		6-34-4		—		—	

Magnet Coils

Coil Suffix

120V 60 Hz or 110V 50 Hz	A	9-1887-1		9-1889-1		9-2526-1		9-1891-1		9-1889-1
240V 60 Hz or 220V 50 Hz	B	9-1887-2		9-1889-2		9-2526-2		9-1891-2		9-1889-2
480V 60 Hz or 440V 50 Hz	C	9-1887-3		9-1889-3		9-2526-3		9-1891-3		9-1889-3
600V 60 Hz or 550V 50 Hz	D	9-1887-4		9-1889-4		9-2526-4		9-1891-4		9-1889-4
208V 60 Hz	E	9-1887-5		9-1889-13		9-2526-5		9-1891-13		9-1889-13
24V 60 Hz	T	9-1887-7		9-1889-20		9-2526-6		9-1891-15		9-1889-20
380V 50 Hz	L	9-1887-8		9-1889-14		9-2526-7		9-1891-14		9-1889-14
120/240V 60 Hz or 110/220V 50 Hz	F	—		9-1890-1		—		—		—
277V 60 Hz	H	9-1887-16		9-1889-31		9-2526-15		9-1891-26		9-1889-31
120V DC	A1	9-2024-2		9-2025-2		9-2626-2		9-2026-2		9-2025-2
240V DC	B1	9-2024-1		9-2025-1		9-2626-1		9-2026-1		9-2025-1
24V DC	T1	9-2024-4		9-2025-4		9-2626-4		9-2026-4		9-2025-4
48V DC	W1	9-2024-3		9-2025-3		9-2626-3		9-2026-3		9-2025-3

Replacement Thermal Elements

Standard Trip Eutectic (12 teeth)	10-4767		10-4767		10-4767		10-4767		10-4767	
Slow Trip Eutectic (24 teeth)	10-5018		10-5018		10-5018		10-5018		10-5018	
Current Transformer	—		—		—		—		—	

Description	Size 4		Size 5		Size 6					
	Part Number	Price U.S. \$	Part Number	Price U.S. \$	Series A1		Series B1		Series C1	
					Part Number	Price U.S. \$	Part Number	Price U.S. \$	Part Number	Price U.S. \$

Set of Contacts

Part Number on Contactor or Starter Nameplate										
2-Pole without Interlock	6-36-3 ①		6-27		6-28		—		6-601-2	
3-Pole without Interlock	6-36-4 ①		6-27-2		6-28-2		6-570		6-601	
3-Pole with Interlock	—		—		—		—		—	
4-Pole without Interlock	—		—		—		—		—	
5-Pole without Interlock	—		—		—		—		—	

Magnet Coils

Coil Suffix

120V 60 Hz or 110V 50 Hz	A	9-1891-1		9-1891-1		9-1875-1		9-2651		9-2698
240V 60 Hz or 220V 50 Hz	B	9-1891-2		9-1891-2		9-1875-2		9-2651-2		9-2698-2
480V 60 Hz or 440V 50 Hz	C	9-1891-3		9-1891-3		9-1875-3		9-2651-3		9-2698-3
600V 60 Hz or 550V 50 Hz	D	9-1891-4		9-1891-4		9-1875-4		9-2651-4		9-2698-4
208V 60 Hz	E	9-1891-13		9-1891-13		9-1875-14		9-2651-6		9-2698-5
24V 60 Hz	T	9-1891-15		9-1891-15		—		—		—
380V 50 Hz	L	9-1891-14		9-1891-14		—		9-2651-5		9-2698-6
120/240V 60 Hz or 110/220V 50 Hz	F	—		—		—		—		—
240/480V 60 Hz or 220/440V 50 Hz	G	—		—		—		—		—
277V 60Hz	H	9-1891-26		9-1891-26		—		—		—
120V DC	A1	9-2026-2		9-2026-2		—		—		—
240V DC	B1	9-2026-1		9-2026-1		—		—		—
24V DC	T1	9-2026-4		9-2026-4		—		—		—
48V DC	W1	9-2026-3		9-2026-3		—		—		—

Replacement Thermal Elements

Standard Trip Eutectic (12 teeth)	10-4767		10-4767		10-4767		10-4767		10-4767	
Slow Trip Eutectic (24 teeth)	10-5018		10-5018		—		—		—	
Current Transformer	—		—		—		—		—	

① #Series B1. For Series A1, order 6-26 or 6-26-2.

Renewal Parts

33

Table 33-357. Citation Renewal Parts (Continued)

Description	Size 7				Size 8	
	Series A1	Price U.S. \$	Series B1	Price U.S. \$	Part Number	Price U.S. \$
	Part Number		Part Number			
Set of Contacts						
Part Number on Contactor or Starter Nameplate						
2-Pole without Interlock	6-28		—		—	
3-Pole without Interlock	6-28-2		6-570		6-571	
3-Pole with Interlock	—		—		—	
4-Pole without Interlock	—		—		—	
5-Pole without Interlock	—		—		—	
Magnet Coils						
	Coil Suffix					
120V 60 Hz or 110V 50 Hz	A	9-1875-1		9-2651		9-2654
240V 60 Hz or 220V 50 Hz	B	9-1875-2		9-2651-2		9-2654-2
480V 60 Hz or 440V 50 Hz	C	9-1875-3		9-2651-3		9-2654-3
600V 60 Hz or 550V 50 Hz	D	9-1875-4		9-2651-4		9-2654-4
208V 60 Hz	E	9-1875-14		9-2651-6		9-2654-6
24V 60 Hz	T	—		—		—
380V 50 Hz	L	—		9-2651-5		9-2654-5
120/240V 60 Hz or 110/220V 50 Hz	F	—		—		—
240/480V 60 Hz or 220/440V 50 Hz	G	—		—		—
277V 60 Hz	H	—		—		—
120V DC	A1	—		—		—
240V DC	B1	—		—		—
24V DC	T1	—		—		—
48V DC	W1	—		—		—
Replacement Thermal Elements						
Standard Trip Eutectic (12 teeth)		10-4767		10-4767		10-4767
Slow Trip Eutectic (24 teeth)		—		—		—
Current Transformer		—		—		—

Discount Symbol **1CD1C**

For Type N Control

Table 33-358. Contact Kits

Poles	NEMA Size	Part Number	Price U.S. \$
3	0	1605226	
	1	1605212	
	2	1605202	
	3	1625563	
	4	1625564	

Table 33-359. AC Coils

Voltage	Hz	2-, 3-Pole			4-, 5-Pole		
		Obsolete Part Number	Current Part Number	Price U.S. \$	Obsolete Part Number	Current Part Number	Price U.S. \$

Size 0, 1 ①

110	60	1470241	9969D90G01		1470261	9969D90G16	
110/208/220	25/60/60	1470242	9969D90G02		1470262	9969D90G17	
220/380/440	25/50/60	1470243	9969D90G03		1470263	9969D90G18	
550	60	1470244	9969D90G04		N/A	N/A	
220	50	1470247	9969D90G06		N/A	N/A	
440	50	1470248	9969D90G07		1470268	9969D90G19	
440	25	1470250	9969D90G08		1470270	9969D90G21	
120	60	1605268	9969D90G09		N/A	N/A	
115/208/230	60/60/60	1605513	9969D90G15		N/A	N/A	
600	60	1470245	9969D90G20		N/A	N/A	
550	25	1470251	9969D90G22		N/A	N/A	

Size 2 ①

110	60	1470201	9969D92G01		1470221	9969D93G01	
110/208/220	25/60/60	1470202	9969D92G02		1470222	9969D93G02	
220/380/440/480	25/50/60/60	1470203	9969D92G03		N/A	N/A	
550	60	1470204	9969D92G04		1470224	9969D93G10	
110	50	1470206	9969D92G05		1470226	9969D93G05	
220	50	1470207	9969D92G06		1470227	9969D93G06	
440	50	1470208	9969D92G07		N/A	N/A	
600	60	1470205	9969D92G08		1470225	9969D93G08	
440	25	1470210	9969D92G09		N/A	N/A	
120/110	60/50	1605478	9969D92G10		N/A	N/A	
550	50	1470209	9969D92G11		N/A	N/A	
415	50	N/A	N/A		L1557647	9969D93G09	
220/380/440	25/60/60	N/A	N/A		1470223	9969D93G03	

Size 3 ①

110	60	1490645	9969D96G04		1490645	9969D96G04	
110/208/220	25/60/60	1490646	9969D96G05		1490646	9969D96G05	
220/380/400/440	25/50/50/60	1490647	9969D96G06		1490647	9969D96G06	
110	50	1490652	9969D96G08		1490652	9969D96G08	
120/110	60/50	1600770	9969D96G09		1600770	9969D96G09	
600/500	60/50	1490649	9969D96G21		1490649	9969D96G21	
600/500/400	60/50/40	1659421	9969D96G23		1659421	9969D96G23	
220	50	1490653	9969D93G24		1490653	9969D93G24	
240	60	1490648	9969D96G29		1490648	9969D96G29	

Size 4

110	60	1596633	9969D96G10		1597723	9969D96G01	
110/208/220	25/60/60	1490658	9969D96G11		1597724	9969D96G02	
110	50	1596636	9969D96G13		N/A	N/A	
220	50	1596637	9969D96G14		N/A	N/A	
240	50	1596639	9969D96G15		N/A	N/A	
600/500	60/50	1596635	9969D96G16		1490649	9969D96G21	
440	25	1596641	9969D96G17		N/A	N/A	
600	60	1596634	9969D96G19		N/A	N/A	
440	60	1490659	9969D96G12		N/A	N/A	
120/110	60/50	1600771	9969D96G20		N/A	N/A	
220/380/400/440	25/50/50/60	N/A	N/A		1597725	9969D96G31	

① Minimum order quantity of 3 required.