

Outlet Boxes Super-Safeway™ Series 3000 Boxes and Coverplates, Yellow

Features and Benefits

- NEōTEX® Paracril OZO rubber double-sided portable outlet boxes yield the best performance for abrasion, chemical exposure and temperature extremes
- Many non-receptacle options provide complete flexibility to create your own solution
- Select either double C-cord clamps or MAX-LOC® strain relief for optimum life

Reference Information

UL File No.: E46237
CSA File No.: LR6837




Physical

Double-sided portable outlet box: NEōTEX Paracril OZO rubber
Receptacle Coverplate: Nylon, polycarbonate, polypropylene
Cover and Receptacle Face Screws: Stainless Steel

Environmental

Rating: General industrial duty



C-Clamp

One F (X) Fitting

Two F (X) Fittings

Standard and Extended Depth, Dual-Sided, 2 Receptacle Box

| Description | Cord Diameter | Box Only | | Box with Duplex Plates | | Box with Dual Flip Lids | |
|-------------------------------------|----------------------------|--------------|-------------|------------------------|-------------|-------------------------|-------------|
| | | Woodhead No. | Order No. | Woodhead No. | Order No. | Woodhead No. | Order No. |
| Standard depth, C-clamp | 8.26-16.64mm 0.325-0.655" | 3050 | 130137-0147 | 3000 | 130137-0087 | | |
| Standard depth, one (F2) | 7.92-15.88mm 0.312-0.625" | 3059 | 130137-0149 | | | 3005 | 130137-0126 |
| Standard depth, feed-thru, two (F2) | 7.92-15.88mm 0.312-0.625" | 3050F | 130137-0148 | | | | |
| Extended depth, C-Clamp | 8.26-16.64mm 0.325-0.655" | 3090 | 130137-0013 | 3080 | 130137-0007 | | |
| Extended depth, One (F3) | 12.70-19.05mm 0.500-0.750" | 3099 | 130137-0216 | | | 3085 | 130137-0010 |
| Extended depth, feed-thru, two (F3) | 12.70-19.05mm 0.500-0.750" | 3090F | 130137-0204 | 3080F | 130137-0176 | 3085F | 130137-0199 |
| Extended depth, one (F4) | 19.05-24.64mm 0.750-0.970" | 3091 | 130137-0014 | | | | |
| Extended depth, feed-thru, two (F4) | 19.05-24.64mm 0.750-0.970" | 3091F | 130137-0210 | | | | |

| Description | Cord Diameter | 1.39" Diameter* | | | | 1.56" Diameter† | | | |
|-------------------------------------|----------------------------|-----------------------------------|-------------|-------------------------------------|-------------|-----------------------------------|-------------|-------------------------------------|-------------|
| | | Box with Plates Straight Blade | | Box with Flip Lids Locking Blade | | Box with Plates Straight Blade | | Box with Flip Lids Locking Blade | |
| | | Woodhead No. | Order No. | Woodhead No. | Order No. | Woodhead No. | Order No. | Woodhead No. | Order No. |
| Standard depth, C-clamp | 8.26-16.64mm 0.325-0.655" | 3001 | 130137-0121 | | | 3003 | 130137-0124 | | |
| Extended depth, C-Clamp | 8.26-16.64mm 0.325-0.655" | 3081 | 130137-0008 | | | 3083 | 130137-0185 | | |
| Extended depth, one (F3) | 12.70-19.05mm 0.500-0.750" | | | 3086 | 130137-0011 | | | 3082 | 130137-0009 |
| Extended depth, feed-thru, two (F3) | 12.70-19.05mm 0.500-0.750" | | | 3086F | 130137-0006 | | | | |

* 15A and 20A NEMA straight blade, 15A NEMA locking

† 20A NEMA locking

Outlet Boxes Super-Safeway™ Series 3000 Boxes and Coverplates, Yellow

Features and Benefits

- NEoTEX® Paracril OZO rubber double-sided portable outlet boxes yield the best performance for abrasion, chemical exposure and temperature extremes
- Many non-receptacle options provide complete flexibility to create your own solution
- Select either double C-cord clamps or MAX-LOC® strain relief for optimum life

Physical

Double-sided portable outlet box: NEoTEX Paracril OZO rubber


Receptacle Coverplate: Nylon, polycarbonate, polypropylene

Cover and Receptacle Face Screws: Stainless Steel

Environmental

Rating: General industrial duty

Power Distribution



Coverplate

| Description | Duplex Opening | | Duplex Flip Lid | | 1.39" Diameter* | | | | 1.56" Diameter† | | | |
|-------------|----------------|-------------|-----------------|-------------|-----------------|-------------|--------------|-------------|-----------------|-------------|--------------|-------------|
| | Woodhead No. | Order No. | Woodhead No. | Order No. | Opening | | Flip Lid | | Opening | | Flip Lid | |
| | | | | | Woodhead No. | Order No. | Woodhead No. | Order No. | Woodhead No. | Order No. | Woodhead No. | Order No. |
| Coverplate | 3051 | 130138-0020 | 3056 | 130138-0025 | 3052 | 130138-0022 | 3057 | 130138-0028 | 3055 | 130138-0024 | 3058 | 130138-0029 |

* 15 and 20A NEMA straight blade, 15A NEMA locking

† 20A NEMA locking



| Description | Blank Plate | | GFCI Opening | | GFCI Flip Lid | | GFCI Clear Silicone Watertite® | |
|-------------|--------------|-------------|--------------|-------------|---------------|-------------|--------------------------------|-------------|
| | Woodhead No. | Order No. | Woodhead No. | Order No. | Woodhead No. | Order No. | Woodhead No. | Order No. |
| Coverplate | 3054 | 130138-0023 | 3060 | 130138-0030 | 3061 | 130138-0032 | 3363 | 130138-0048 |