



Features:

- Universal / Full Range Input
- Interchangeable AC Heads
- Level 6 Efficiency
- Cost Effective & Highly Reliable
- 1 Year Warranty



Characteristics						
Part Number	T5884ST	T5885ST	T5886ST	T5887ST	T5888ST	T5781ST
Model Designation	6A-06IWP					
Output Voltage	5Vdc	9Vdc	12Vdc	15Vdc	24Vdc	12Vdc
Output Current Max	1.2A	0.67A	0.5A	0.4A	0.25A	0.5A
Output Current Min	0A	0A	0A	0A	0A	0A
Power (Watts)	6W	6W	6W	6W	6W	6W
Line Regulation	+/- 3%					
Voltage Tolerance	+/- 3%					
Ripple & Noise (mV p-p)	<150mV (p-p)	<150mV (p-p)	<200mV (p-p)	<200mV (p-p)	<300mV (p-p)	<200mV (p-p)
Protections	Over Voltage Protection Short Circuit Protection					
Rated Input Voltage	100 - 240Vac					
Full Input Voltage Range	90Vac - 264Vac					
Rated Frequency	50 - 60Hz					
Full Frequency Range	47 - 63Hz					
Efficiency	75.1%	78.8%	78.8%	78.8%	78.8%	78.8%
Input Current (RMS Max)	300mA					
Inrush Current	No Damage					
Leakage Current	<0.25mA					
Input Power (no load)	<0.1W					
AC Inlet	Interchangeable UK, Euro & US Plugtop					
DC Cord	1.5M Cable	1.5M Cable	1.5M Cable	1.5M Cable	1.5M Cable	1.5M Cable
DC Plug	2.1mm C+Ve	2.1mm C+Ve	2.1mm C+Ve	2.1mm C+Ve	2.1mm C+Ve	2.5mm C+Ve
Hi-Pot Specification	3000Vac or 4242Vdc 10mA 1 min. (I.P. to O.P.)					
Insulation Resistance	500Vdc to test the I.P.-O.P resistance is not less than 100Mohm (I.P. to O.P.)					
Operating Temperature	0C to 40C					
Storage Temperature	-10C to 70C					
Operating Humidity	20 % to 80%					
Storage Humidity	10% to 90%					
Safety Approvals	UL/CUL, CE, CB, GS, RCM,					
PB-Free	Yes - RoHS Compliant					
Weight	116g					108g
Dimensions (mm)	64 x 40.5 x 30					