



### Features:

- Universal / Full Range Input
- Interchangeable AC Heads
- Level 6 Efficiency
- Cost Effective & Highly Reliable
- 1 Year Warranty



Characteristics		
Part Number	T5776ST	T5778ST
Model Designation	6A-401WP	
Output Voltage	12Vdc	24Vdc
Output Current Max	3A	1.7A
Output Current Min	0A	0A
Power (Watts)	40W	40W
Line Regulation	+/- 1%	
Voltage Tolerance	+/- 5%	
Ripple & Noise (mV p-p)	<120mV (p-p)	<200mV (p-p)
Protections	Over Voltage Protection Short Circuit Protection Over Load Protection	
Rated Input Voltage	100 - 240Vac	
Full Input Voltage Range	90Vac - 264Vac	
Rated Frequency	50 - 60Hz	
Full Frequency Range	47 - 63Hz	
Efficiency	87.4%	87.6%
Input Current (RMS Max)	1A	
Inrush Current	No Damage	
Leakage Current	<0.25mA	
Input Power (no load)	<0.1W	
AC Inlet	Interchangeable UK, Euro & US Plugtop	
DC Cord	1.5M Cable	1.5M Cable
DC Plug	2.1mm C+Ve	2.1mm C+Ve
Hi-Pot Specification	3000Vac or 4242Vdc 10mA 1 min. (I.P. to O.P.)	
Insulation Resistance	500Vdc to test the I.P.-O.P resistance is not less than 100Mohm (I.P. to O.P.)	
Operating Temperature	0C to 40C	
Storage Temperature	-10C to 70C	
Operating Humidity	20 % to 80%	
Storage Humidity	10% to 90%	
Safety Approvals	UL/CUL, CE, CB, GS, RCM,	
PB-Free	Yes - RoHS Compliant	
Dimensions (mm)	90 x 38 x 59.4	