

Main

Range of product	TeSys D TeSys D control relay
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	LC1D09...D38 LC1DT20...DT40

Complementary

Mounting location	Side
Mounting mode	By clips
Suppressor technology	Bidirectional peak limiting diode
Control circuit voltage	24 V DC
Maximum peak voltage	2 Uc
Product weight	0.012 kg

Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Contractual warranty

Period	18 months
--------	-----------