

TLS 2200® Thermal Label Printer



TLS 2200® THERMAL LABELING SYSTEM

- Permanent, Quick, Crisp Labels
- Built-in Electrical and Voice/Data Symbols
- Autotext Sizing TLS 2200® reads your label size and style, selects the most suitable type size, and instantly registers it for printing
- Variable Font Sizes from 1 (4 point) to 19 (72 point)


TLS 2200® & Accessories

Catalog #	Description	Price
TLS2200	Printer (Includes hard case, battery pack, battery charger, test labels (PTL-19-423), R6210 ribbon, cleaning strip, communications cable, manual and Quick Start Guide)	\$795.00
R4310	Black Ribbon	\$26.83
R6010	Black Ribbon	\$26.83
R6210	Black Ribbon	\$26.83
TLS2200-AC	AC Power Supply	\$117.93
TLSHM-QUICKCH	Battery Quick Charger	\$115.49



Interactive Demo


View an online interactive demo of TLS 2200® printer. To view visit: www.bradysid.com/tls2200



General Adhesive Wire & Cable Markers

- Industrial strength Vinyl Cloth (B498) and Nylon Cloth (B499) designed to conform to curved surfaces
- Printer automatically calibrates label and prints multiple lines of wire code legend

Wire Gauge	Material	Part Number	Labels/ Roll	Label Dimensions		Maximum Characters/ Line For Font:			Maximum Lines Of Text For Font:			Price
				Inch (mm) A	Inch (mm) B	2	7	10	2	7	10	
16 to 22	Vinyl Cloth	PTL-7-498	500	0.500 (12.70)	0.500 (12.70)	11	5	3	5	2	1	\$45.94
10 to 16	Vinyl Cloth	PTL-10-498	750	0.250 (6.35)	0.750 (19.05)	5	2	1	3	1	1	\$47.88
10 to 16	Vinyl Cloth	PTL-11-498	500	0.500 (12.70)	0.750 (19.05)	11	5	3	8	4	2	\$44.79
10 to 12	Vinyl Cloth	PTL-16-498	500	0.375 (9.52)	1.000 (25.40)	8	3	2	10	5	3	\$51.31
10 to 12	Nylon Cloth	PTL-16-499	500	0.375 (9.52)	1.000 (25.40)	8	3	2	10	5	3	\$52.77
10 to 12	Vinyl Cloth	PTL-17-498	500	0.500 (12.70)	1.000 (25.40)	11	5	3	3	1	1	\$34.57
10 to 12	Vinyl Cloth	PTL-18-498	250	0.750 (19.05)	1.000 (25.40)	18	7	5	10	5	3	\$35.31
10 to 12	Nylon Cloth	PTL-18-499	250	0.750 (19.05)	1.000 (25.40)	18	7	5	10	5	3	\$37.51
10 to 12	Vinyl Cloth	PTL-19-498	250	1.000 (25.40)	1.000 (25.40)	24	10	7	10	5	3	\$38.36
10 to 12	Nylon Cloth	PTL-19-499	250	1.000 (25.40)	1.000 (25.40)	24	10	7	10	5	3	\$48.75
4 to 10	Vinyl Cloth	PTL-28-498	750	0.250 (6.35)	1.500 (38.10)	5	2	1	16	8	5	\$49.97
4 to 10	Nylon Cloth	PTL-28-499	750	0.500 (12.70)	0.500 (12.70)	5	2	1	16	8	5	\$46.67
4 to 10	Vinyl Cloth	PTL-29-498	500	0.500 (12.70)	0.500 (12.70)	11	5	3	16	8	5	\$47.64
4 to 10	Nylon Cloth	PTL-29-499	500	0.500 (12.70)	1.500 (38.10)	11	5	3	16	8	5	\$41.06
4 to 10	Vinyl Cloth	PTL-30-498	250	0.750 (19.05)	1.500 (38.10)	18	7	5	16	8	5	\$42.16
4 to 10	Nylon Cloth	PTL-30-499	250	0.750 (19.05)	1.500 (38.10)	18	7	5	16	8	5	\$47.64
4 to 10	Vinyl Cloth	PTL-31-498	250	1.000 (25.40)	1.500 (38.10)	24	10	7	16	8	5	\$48.87
4 to 10	Nylon Cloth	PTL-31-499	250	1.000 (25.40)	1.500 (38.10)	24	10	7	16	8	5	\$30.67
Lg. Cable	Vinyl Cloth	PTL-21-498	100	1.000 (25.40)	2.500 (63.50)	24	10	7	23	14	9	\$36.66
Lg. Cable	Vinyl Cloth	PTL-23-498	100	1.000 (25.40)	4.000 (101.60)	24	10	7	23	22	15	\$40.93
Lg. Cable	Vinyl Cloth	PTL-34-498	50	1.500 (38.10)	6.000 (152.40)	37	15	10	64	32	21	



Self-Laminating Adhesive Wire & Cable Markers

- Extra-durable B427 material features a clear trailer that wraps over print area to protect the printed text
- Exceptional adhesion to Cat. 5 cable and electrical wires and cable

Application	Material	Part Number	Labels/ Roll	Label Dimensions			Max. Characters/ Line For Font:			Max. Lines Of Text For Font:			Price
				Inch (mm) A	Inch (mm) B	Inch (mm) C	2	7	10	2	7	10	
2 pair Fiber, Single/Multi-Mode	Vinyl Self-lam.	PTL-19-427	250	1.000 (25.40)	1.000 (25.40)	0.375 (9.53)	24	10	7	3	1	1	\$36.77
25 pair Copper, 4-12 pair Fiber	Vinyl Self-lam.	PTL-21-427	100	1.000 (25.40)	2.500 (63.50)	0.750 (19.05)	24	10	7	8	4	2	\$32.01
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-64-427	100	1.000 (25.40)	3.375 (85.73)	1.125 (28.58)	24	10	7	12	12	8	\$15.64
50 pair Copper, 24 pair Fiber	Vinyl Self-lam.	PTL-23-427	100	1.000 (25.40)	4.000 (101.60)	1.000 (25.40)	24	10	7	10	5	3	\$38.12
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-29-427	500	0.500 (12.70)	1.500 (38.10)	0.500 (12.70)	11	5	3	5	2	1	\$56.94
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-30-427	250	0.750 (19.05)	1.500 (38.10)	0.500 (12.70)	18	7	5	5	2	1	\$42.28
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-31-427	250	1.000 (25.40)	1.500 (38.10)	0.500 (12.70)	24	10	7	5	2	1	\$54.50
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-32-427	250	1.500 (38.10)	1.500 (38.10)	0.500 (12.70)	37	15	10	5	2	1	\$54.86
50 pair Copper, 24 pair Fiber	Vinyl Self-lam.	PTL-33-427	100	1.500 (38.10)	4.000 (101.60)	1.000 (25.40)	37	15	10	10	5	3	\$51.56
100 pair Copper, 36 pair Fiber	Vinyl Self-lam.	PTL-34-427	50	1.500 (38.10)	6.000 (152.40)	1.500 (38.10)	37	15	10	16	8	5	\$34.09