


U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® GMP-GL	07.11.2014

Glass fibre-reinforced for maximum mechanical stability
Supporting surface for spanner means scratches on the housing are avoided



Assembly time



Temperature-resistant



Variety of approval certifications

Application range

For locking SKINTOP® cable glands in boreholes without thread.

Product Make-up

PG connection thread

Norm references / Approvals

UL File Nr. E79903

Note

UL approval only when used with the UL-approved SKINTOP® polyamide cable glands
Designed for use with SKINTOP® ST(R)

Remark


Photographs are not to scale and do not represent detailed images of the respective products.


Technical Data

On request:	Available without collar (without surface for assembling tool)
Classification:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: cable screw gland
Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Polyamide, glass fibre-reinforced
Temperature range:	-20°C to +100°C

Product Management	Document: LAPP_PRO1073EN.pdf	1 / 3
--------------------	------------------------------	-------

Part number	Article designation / size	SW (mm)	Pieces / PU
SKINTOP® GMP-GL silver grey with collar			
53019000	GMP-GL 7	19	100
53019010	GMP-GL 9	22	100
53019020	GMP-GL 11	24	100
53019030	GMP-GL 13,5	27	100
53019040	GMP-GL 16	30	100
53019050	GMP-GL 21	36	50
53019060	GMP-GL 29	46	50
53019070	GMP-GL 36	60	25
53019080	GMP-GL 42	65	25
53019090	GMP-GL 48	70	25
SKINTOP® GMP-GL black with collar			
53019200	GMP-GL 7	19	100
53019210	GMP-GL 9	22	100
53019220	GMP-GL 11	24	100
53019230	GMP-GL 13,5	27	100
53019240	GMP-GL 16	30	100
53019250	GMP-GL 21	36	50
53019260	GMP-GL 29	46	50
53019270	GMP-GL 36	60	25
53019280	GMP-GL 42	65	25
53019290	GMP-GL 48	70	25
SKINTOP® GMP-GL light grey with collar			
53019001	GMP-GL 7	19	100
53019011	GMP-GL 9	22	100
53019021	GMP-GL 11	24	100
53019031	GMP-GL 13,5	27	100
53019041	GMP-GL 16	30	100
53019051	GMP-GL 21	36	50
53019061	GMP-GL 29	46	50
53019071	GMP-GL 36	60	25
53019081	GMP-GL 42	65	25
53019091	GMP-GL 48	70	25

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® GMP-GL	07.11.2014



Product Management	Document: LAPP_PRO1073EN.pdf	3 / 3
--------------------	------------------------------	-------