

INTRODUCING...

THE NEW AND EXCITING Han[®] "LITE" SAMPLE CASE!!



Featuring Many New HARTING Products Including:

- **Han[®] Port** – An interface that provides a convenient and environmentally protected method of accessing enclosures
- **Identification Module** – An “intelligent” connector that offers non-volatile decentralized storage of operating data for machine components
- **Han-Quintax[®] 3A** – Provides a space-saving, industrially-protected connector solution for sensitive signaling and Ethernet communication



Case Characteristics:

- Constructed with durable black vinyl material, making the case water and stain resistant
- Compact size allows for easy handling (Dimensions: 18” x 12”)
- Lightweight (Only 10lbs. Fully assembled!)
- Shoulder strap included
- Red vinyl table top protector included

PLUS MUCH MORE!!!!!!!!!!!!!!!!!!!!

Use This Part Number To Order Your Own
Fully-Assembled Han “Lite” Sample Case:
73 55 040 0101

*Distributor Net Price: \$330

SAMPLE CASE CONTENTS

Location	Part Number	Qty	Description	Catalog Page
1	09 00 000 5017	1	Cable Sealing Metal (IP 65) with Multiple Seal	40.08
1	09 30 024 0301	1	24 B Housing Bulkhead Mounting	30.19
1	09 30 024 0421	1	24 B Top Entry Hood	30.18
1	09 32 046 3001	1	46 EE Male Crimp Insert	03.27
1	09 32 046 3101	1	46 EE Female Crimp Insert	03.27
1	09 33 000 6102	46	2.5mm ² Male E Pins	01.15
1	09 33 000 6202	46	2.5mm ² Female E Pins	01.15
2	09 16 042 3001	1	42 DD Male Crimp Insert	02.25
2	09 15 000 6106	42	2.5mm ² Male D Pins	02.12
3	09 11 001 2652	1	350 Amp HC Module Male	14.15
4	09 11 001 2752	1	350 Amp HC Module Female	14.15
5	09 00 000 5059	1	Q 8/0 Cable Gland Thermoplastic PG 16	13.16
5	09 12 008 0327	1	Q 8/0 Housing Bulkhead Mounting Thermoplastic	13.17
5	09 12 008 0527	1	Q 8/0 Hood Thermoplastic	13.16
5	09 12 008 3001	1	Q 8/0 Male Crimp Insert	13.15
5	09 12 008 3101	1	Q 8/0 Female Crimp Insert	13.15
5	09 33 000 6102	9	2.5mm ² Male E Pins	01.15
5	09 33 000 6202	9	2.5mm ² Female E Pins	01.15
6	09 00 000 5350	1	Blind Grommet	40.05
6	09 30 024 0408	1	Han Split Hood 24 B	40.05
6	09 00 000 5353	1	Cable Entry Gland	40.05
6	09 00 000 5358	1	Cable Entry Gland	40.05
6	09 00 000 5362	1	Cable Entry Gland	40.05
7	09 12 004 2611	1	Han-Brid Male	Data Sheet
7	09 12 004 2711	1	Han-Brid Female	Data Sheet
7	09 20 003 0320	1	3A Plastic Housing Bulkhead Mounting	30.10
7	09 20 003 0420	1	3A Plastic Hood Top Entry	30.10
7	09 15 000 6102	5	1.0mm ² Male D Pins	02.12
7	09 15 000 6202	5	1.0mm ² Female D Pins	02.12
8	09 30 006 0442	1	6 B Top Entry Hood	30.16
8	09 33 006 2616	1	6 ES Male Cage-Clamp Insert	03.14
9	09 33 006 4725	1	6 E Female Terminal Block Insert	08.15
10	21 01 130 4061	1	M8 3p Male Straight	50.20


SAMPLE CASE CONTENTS

Location	Part Number	Qty	Description	Catalog Page
11	21 01 140 4091	1	M12 4p HARAX Straight	50.20
12	21 03 212 1305	1	HARAX M12L 4 pole male	50.20
12	21 03 212 2305	1	HARAX M12L 4 pole female	50.20
13	09 33 000 9989	1	Han Snap - Din Rail Mount	11.15
14	09 62 000 5008	1	PG 21 EMC Cable Clamp (IP 68)	40.09
15	09 00 000 5093	1	PG 21 Universal Cable Protection (IP 68)	40.08
16	09 12 003 3001	1	Han 3A Cable Side (Male) RJ-45 without PCB	Data Sheet
16	09 12 003 2794	1	Panel Feed Through w/2x RJ-45 Jack	Data Sheet
16	09 20 003 0301	1	Han 3A Housing Bulkhead Mounting	30.11
16	09 20 003 1443	1	Han 3A Top Entry Hood Metal	30.11
16	09 15 000 6102	2	1.0mm ² Male D Pins	02.12
16	09 15 000 6202	2	1.0mm ² Female D Pins	02.12
17	73 55 040 0915	1	Han Port RJ-45 120VAC 3A	Flyer
18	09 38 006 2601	1	4/2 K Male Insert Screw Terminal	05.15
18	09 38 006 2701	1	4/2 K Female Insert Screw Terminal	05.15
19	09 20 003 0440	1	Han 3A with HARAX (Male Version)	01.12
20	09 20 004 2611	1	4A Male Insert	01.12
20	09 20 004 2711	1	4A Female Insert	01.12
20	09 40 003 0301	1	3A HPR Housing Bulkhead Mounting with Sealing Screw	30.30
20	09 40 003 0402	1	3A HPR Hood with Sealing Screw	30.30
21	09 15 003 3001	1	Han Quintax 3A Male Insert	Data Sheet
21	09 15 003 3101	1	Han Quintax 3A Female Insert	Data Sheet
21	09 15 004 3013	1	Quintax Z Contact Male	06.33
21	09 15 004 3113	1	Quintax Z Contact Female	06.33
21	09 15 000 6102	6	Male Crimp Contacts	02.12
21	09 15 000 6202	6	Female Crimp Contacts	02.12
21	09 20 003 1443	1	Han 3A Top Entry Hood Metal	30.11
21	09 20 003 0301	1	Han 3A Bulkhead Mounted Housing Metal	30.11
22	09 14 000 6274	2	6mm Female Pneumatic Contact	06.31
22	09 14 002 2751	1	100 A Module Female Axial Screw Termination	06.11
22	09 14 025 3001	1	Male D-Sub Module	06.25

SAMPLE CASE CONTENTS

Location	Part Number	Qty	Description	Catalog Page
22	09 14 025 3101	1	Female D-Sub Module	06.25
22	09 14 002 4501	2	Pneumatic Module	06.31
22	09 14 008 3101	1	Han 8 EE Module Female	06.19
22	09 14 024 0303	1	24 B Hinged Frame (A...F)	06.09
22	09 33 000 6104	8	1.5mm^2 Male E pin	01.15
22	09 14 024 0313	1	24 B Hinged Frame (a...f)	06.09
22	09 14 008 3001	1	Han 8 EE Module Male	06.19
22	09 14 002 2651	1	100 A Module Male Axial Screw Termination	06.11
22	09 14 000 6174	2	6mm Male Pneumatic Contact	06.31
22	09 33 000 6204	8	1.5mm^2 Female E pin	01.15
22	09 14 000 9950	2	Blank Module (Dummy)	06.34
23	73 55 042 0044	1	ID Module (Dummy)	Data Sheet
<i>ENCLOSED LITERATURE</i>				
	73 55 000 0046	1	Han "Lite" Cover Sheet	
	98 42 020 0201	1	Short Form Han Catalog	20 4
	73 55 000 0045	1	Han Port Flyer	
	73 55 000 0048	1	ID Module Data Sheet	
	73 55 000 0049	1	Han-Brid Industrial Network Interfaces Data Sheet (Includes Han-Brid RJ-45 and Han Quintax 3A)	
	98 42 914 0401	1	HMI 2003 Catalog	

Han[®] “Lite” Reference Diagram



HARTING, Inc. of North America
1370 Bowes Road
Elgin, IL 60123
Phone: 1-866-278-0306
Fax: (847) 741-8257