

KFM
KFK025822



KFM-1/AH 5D 3C Wh

KFM has a sturdy all-metal construction with a sleek design, flexible arm and excellent light output suitable for a variety of industrial, laboratory, cosmetology and low-vision application. The flexibility of the neck assembly and patented internal spring 45" K-arm makes exact positioning easy. It has a 1.25X optical-quality glass lens. Edge clamp mount. Color: white.



Optic

Color of reflector	White
Material of diffuser	Polycarbonate
Primary Lens (D)	5
Working distance (mm)	200
Material of reflector	P C
Magnification (X)	2.25

Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100

Body

Body color	White
Body material	Aluminum

Technical data

IP classification	20
-------------------	----

Lightsource

Number of lamps	1
Lamp power (W)	22
Lamp base	G10Q
CRI and/or Color Temperature	4100K
Lightsource	T9

Dimensions

Net weight (kg)	4,7
Gross weight (lb.)	11
Arm length (in.)	45

Termination

Cord length (ft)	6
Mounting	Edge clamp

Ballast

Type of Ballast	High frequency
-----------------	----------------