

Polyester Tape (B-569)

- Outdoor Grade
- Best choice for marking stainless steel pipes & surfaces (low halide content)
- Ultra-smooth finish excellent for mounting to rigid panels & very smooth surfaces.
- Applies best to very smooth surfaces



Figure 33



Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
Fig.33	76614	B-569	White	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76615	B-569	White	3.000 (76.2)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76616	B-569	White	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76617	B-569	White	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76618	B-569	White	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76619	B-569	Yellow	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76620	B-569	Yellow	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76621	B-569	Yellow	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76622	B-569	Yellow	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76623	B-569	Red	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76624	B-569	Red	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76625	B-569	Red	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76626	B-569	Red	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76627	B-569	Blue	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76628	B-569	Blue	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76629	B-569	Blue	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76630	B-569	Blue	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76639	B-569	Green	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76640	B-569	Green	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76641	B-569	Green	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76642	B-569	Green	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76647	B-569	Black	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76648	B-569	Black	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76649	B-569	Black	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76650	B-569	Black	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76643	B-569	Brown	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76644	B-569	Brown	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76645	B-569	Brown	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76646	B-569	Brown	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76602	B-569	Tan	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76603	B-569	Tan	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76604	B-569	Tan	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76605	B-569	Tan	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76651	B-569	Grey	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76652	B-569	Grey	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76653	B-569	Grey	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76654	B-569	Grey	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76631	B-569	Purple	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76632	B-569	Purple	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76633	B-569	Purple	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76634	B-569	Purple	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76635	B-569	Orange	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76636	B-569	Orange	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76637	B-569	Orange	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76638	B-569	Orange	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76598	B-569	Pink	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76599	B-569	Pink	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76600	B-569	Pink	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76601	B-569	Pink	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76606	B-569	Lt. Blue	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76607	B-569	Lt. Blue	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76608	B-569	Lt. Blue	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	76609	B-569	Lt. Blue	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76741
Fig.33	97738	B-569	Ochre	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	97739	B-569	Ochre	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	97740	B-569	Ochre	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	97741	B-569	Ochre	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	97742	B-569	Sky Blue	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	97743	B-569	Sky Blue	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	97744	B-569	Sky Blue	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	97745	B-569	Sky Blue	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76610	B-569	Clear	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76611	B-569	Clear	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76612	B-569	Clear	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	76739
Fig.33	76613	B-569	Clear	0.500 (12.7)	100ft. (30.5m)	1 Roll (cont.)	76739

View all GlobalMark® Print Ribbon parts on page 389.

