

QO110

MINIATURE CIRCUIT BREAKER 120/240V 10A

Product availability: Stock - Normally stocked in distribution facility

Price*: 29.10 USD

Main

Commercial Status	Commercialised
Product or component type	Miniature Circuit Breaker
Range of product	QO
[In] rated current	10 A
Product certifications	CSA UL listed
[Ue] rated operational voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	1P
Short-circuit current	10 kA
Number of spaces required	1
Circuit breaker type	Standard
Circuit breaker application	Not rated
Electrical connection	Pressure plate
AWG gauge	14...8 AWG aluminium 14...8 AWG copper
Accessory / separate part type	None

Ordering and shipping details

Category	00004 - QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
GTIN	00785901205593
Nbr. of units in pkg.	40
Package weight(Lbs)	0.26
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
Product environmental profile	Available

Contractual warranty

Period	18 months
--------	-----------