




Ask for a 2-in-1 that lets you mix work with play.

Buy One. Get Windows 10 free.\*




### Aspire Switch 11 V

The silent performer, powered by an Intel® Core™ M processor and Windows 8.1. Switch effortlessly between 4 modes with Acer Snap Hinge™ 2.



Acer recommends Windows.

**SW5-173** **SPECIFICATIONS**



<b>Product views</b>	1. Keyboard hooks 2. Rear webcam 3. Microphone 4. Headset/speaker jack 5. MicroSD™ card slot	6. HDMI™ micro port 7. Micro USB port 8. DC-in jack for AC adapter 9. Keyboard 10. Keyboard connector	11. Speakers 12. Front webcam 13. Power button 14. Reset pinhole	15. Volume control button 16. Home button 17. USB 2.0 port (on keyboard) 18. Touchpad
<b>Operating system</b>	<b>Windows 8.1 64-bit</b>			
<b>CPU and chipset</b>	<b>Intel® Core™ M-5Y10c processor</b>			
<b>Memory</b> <sup>1,2</sup>	Dual-channel LPDDR3 SDRAM support: 4 GB of onboard LPDDR3 system memory			
<b>Display</b>	11.6" display with IPS (In-Plane Switching) technology <sup>3</sup> , FHD 1920 x 1080 resolution, high-brightness, LED-backlit TFT LCD with integrated multi-touch, supporting 10-finger touch.			
	Wide viewing angle		16:9 aspect ratio	Mercury free, environment friendly
<b>Graphics</b>	<b>Intel® HD Graphics 5300</b>			
<b>Audio</b>	Two built-in stereo speakers Built-in digital microphone			
<b>Storage</b> <sup>4</sup>	<b>Solid State Drive</b> • 128 GB, SATA 3 Gb/s • 60 GB, SATA 3 Gb/s		<b>Card reader</b> • MicroSD™ card	
<b>Webcam</b>	<b>Video conferencing</b> • Acer webcam with 2592 x 1944 resolution and 1080p Full HD audio/video recording • HD webcam with 1280 x 720 resolution and 720p HD audio/video recording			
<b>Wireless and networking</b> <sup>5</sup>	<b>WLAN</b> • Acer InViLink™ Nplify™ 802.11a/b/g/n wireless LAN • Intel® Dual Band Wireless-AC, 802.11ac/a/b/g/n wireless LAN with Acer Nplify™		<b>WPAN</b> • Bluetooth® 4.0	
<b>Privacy controls</b> <sup>1</sup>	BIOS user, supervisor, HDD passwords			
<b>Dimensions and weight</b> <sup>6</sup>	<b>Dimensions</b> • 299.5 (W) 195 (D) x 8.95 (H) mm (11.79 x 7.68 x 0.35 inches; pad only) • 299.5 (W) 206.7 (D) x 20.95 (H) mm (11.79 x 8.14 x 0.82 inches; pad and dock) • 299.5 (W) 206.7 (D) x 23.35 (H) mm (11.79 x 8.14 x 0.92 inches; pad and dock with hard drive)		<b>Weight</b> • 0.77 kg (1.71 lbs.) with 2-cell battery pack; pad only • 1.46 kg (3.22 lbs.) with 2-cell battery pack; pad and dock • 1.57 kg (3.46 lbs.) with 2-cell battery pack; pad and dock with hard drive	
<b>Power adapter and battery</b>	ACPI 5.0 CPU power management standard: supports Standby and Hibernation power-saving modes			
	<b>Power adapter</b> • 3-pin 45 W AC adapter		<b>Battery</b> • 34.5 Wh 4550 mAh 3.8 V 2-cell Li-polymer battery pack • Battery life up to 8 hours	
<b>Input and control</b>	<b>Keyboard:</b> 83-/84-/87-key, full-size Acer FineTip keyboard with international language support <b>Touchpad:</b> Multi-gesture touchpad, supporting two-finger scroll and pinch. Swipes access charms, application commands <b>Control Keys:</b> Power button, volume up and down keys, Windows key			
<b>Sensors</b>	Accelerometer (G-sensor)	E-compass	Intelligent gyroscope	Ambient light sensor
<b>Windows Store apps</b> <sup>7,8</sup>	<b>Acer branded</b> • Acer Explorer			
<b>Windows Desktop apps</b> <sup>7,8</sup>	<b>Acer branded</b> • Acer Care Center • abDocs • abFiles • abMedia	• abPhoto • Acer Hover Access • Acer Portal • Acer Power Management • Acer Recovery Management	• Acer Remote Files • Acer Screen Grasp • Acer Touch Tools • Acer Quick Access • Acer Video Player	<b>Productivity</b> • Office 2013 <sup>9,10</sup> <b>Security</b> • McAfee® Internet Security
<b>Options and accessories</b>	Micro USB 2.0 to USB 2.0 cable			
<b>Warranty</b>	One-year International Travelers Warranty (ITW)			

1. Specifications vary depending on model.  
 2. Shared system memory may be allocated to support graphics, depending on system memory size and other factors. Actual system memory available to the operating system will be reduced by any memory used by the graphics solution and resources required by the operating environment.  
 3. All brands and product names mentioned herein include trademarks of their respective companies and are used solely to describe or identify the products.  
 4. 1 GB is 1 billion bytes. Actual formatted capacity is less and may vary depending on preloaded materials and operating environment. Recovery Management uses a portion of the stated hard disk capacity as dedicated backup space.  
 5. Actual throughput may vary depending on network conditions and environmental factors such as network traffic or overhead, building construction and access point settings.  
 6. The listed battery life is obtained by simulating watching video clips stored on the mobile device. The test clip loops and continues to run, without interruption or any other inputs, until the battery is drained. Stated battery life is for comparison purposes only. Actual battery life varies by model, configuration, applications, power management settings, operating conditions, video clip format, and features used. A battery's maximum capacity decreases with time and use.  
 7. Bundled software may vary depending on hardware configuration, OS and regional availability.  
 8. Trial periods vary depending on the operating system language, geographic region and specifications: 365-day trial for China, Taiwan, Hong Kong and Singapore (Simplified Chinese and Traditional Chinese models); 60-day trial for other regions.  
 9. Some models/configurations have a Microsoft Product Identification (MPI) card in the box, which contains a product key to activate the full version of Microsoft Office 2013 Home and Student Edition. If your device does not include an MPI card, you will need to purchase a product key separately.  
 10. Some models/configurations may activate to a 1 year subscription for Office 365 Personal, depending on the operating system installed.

In a continuing effort to improve the quality of our products, information in this document is subject to change without notice. Images shown are only representations of some of the configurations available for this model. Availability may vary depending on region. As a phenomenon known to thin-film transistors (TFTs), liquid crystal displays (LCDs) commonly exhibit a small number of discoloration dots, as so-called "non-conforming pixels." This phenomenon is a limitation of TFT LCD technology, not a product defect, and as such is not covered by Acer's warranty.  
 © 2015. All rights reserved.  
 Microsoft and Windows are registered trademarks of Microsoft Corporation.  
 Intel, Intel Core, Core Inside, Pentium, and Pentium Inside are trademarks of Intel Corporation in the U.S. and other countries.

**About Acer**

Established in 1976, Acer is a hardware + software + services company dedicated to the research, design, marketing, sale, and support of innovative products that enhance people's lives. Acer's product offerings include PCs, displays, projectors, servers, tablets, smartphones, and wearables. The company is also developing cloud solutions to bring together the Internet of Things. Acer employs 7,000 people and ranks No. 4 for total PCs globally (IDC 2014). Revenues for 2014 reached US\$10.39 billion. Please visit [www.acer.com](http://www.acer.com) for more information.

