

**MNX PCM 95/75 T**



Sample photo

**Order symbol:** PCM 95/75 T  
**Product nbr:** 6016932  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074054807  
**EI. number:**  
 Finland: 3421398  
 Electric No. 8212027598  
 Denmark:  
 Electric No. Sweden: 2535401

Including: Base with metric knock-outs and PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

**Dimensions:** Length Width Height **Accessories:**

<b>mm:</b>	100	100	75	MIN 8	DIN-15 Mounting rail
<b>inch:</b>	3.9	3.9	3.0	B-3	DIN-35 Mounting rail
				FP 22046	Wall fastening lug (4 pcs)

**Materials:** **Rating:**

<b>Material:</b> Polycarbonate	<b>Ingress Protection (EN 60529):</b> IP66/IP67
<b>Base colour:</b> RAL 7035 -light grey	<b>Impact Resistance (EN 62262):</b> IK08
<b>Cover screws material:</b> Polyamide	<b>Electrical insulation:</b> Totally insulated
<b>Cover colour:</b> Smoked grey	<b>Halogen free (DIN/VDE 0472, Part 815):</b> 1
<b>Cover screws colour:</b> Black	<b>UV resistance:</b> UL 508
<b>Gasket material:</b> Polyurethane	<b>Flammability Rating:</b> UL 746C 5V
	<b>Glow Wire Test (IEC 695-2-1) °C:</b> 960
	<b>NEMA Class:</b> NEMA 1, 4, 4X, 6, 12, 13

**Temperatures:** **Certificates:**

<b>Temperature °C (short term):</b> -40 ... 120 °C	<b>Germanischer Lloyd (GL)</b>
<b>Temperature °C (continuous):</b> -40 ... 80 °C	<b>SGS Fimko</b>
<b>Temperature °F (short term):</b> -40 ... 250 °F	<b>Gost R</b>
<b>Temperature °F (continuous):</b> -40 ... 175 °F	

**Accessories:**

MIV 95 Mounting plate (Galvanized steel)

