

MNX PCM 150/100 T



Sample photo

Order symbol: PCM 150/100 T
Product nbr: 6016915
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074038265
EI. number:
 Finland: 3421667
 Electric No. Denmark: 8212027190
 Electric No. Italy: 7342050
 Electric No. Sweden: 2535430

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	180	130	100	MIN 10	DIN-15 Mounting rail
inch:	7.1	5.1	3.9	MIN 15	DIN-15 Mounting rail
				MIV 10	DIN-35 Mounting rail
				MIV 15	DIN-35 Mounting rail

Materials:

Material: Polycarbonate
Base colour: RAL 7035 -light grey
Cover screws material: Polyamide
Cover colour: Smoked grey
Cover screws colour: Black
Gasket material: TPE

Accessories:

FP A 150/180 Front plate (Aluminium)
 HFP 180 Front plate hinge series
 FP 22046 Wall fastening lug (4 pcs)

Temperatures:

Temperature °C (short term): -40 ... 120 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -40 ... 250 °F
Temperature °F (continuous): -40 ... 175 °F

Rating:

Ingress Protection (EN 60529): IP66/IP67
 Impact Resistance (EN 62262): IK08
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 746C 5V
 Glow Wire Test (IEC 695-2-1) °C: 960
 NEMA Class: NEMA 1, 4, 4X, 6

Accessories:

MIV 150 Mounting plate (Galvanized steel)

Certificates:

Germanischer Lloyd (GL)
 SGS Fimko
 Gost R

