


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Interchangeable VDE Screwdriver Blades
Catalogue number	4915
Date	11/08/2015

<p>Range Description Interchangeable VDE Screwdriver Blades</p> <p>Features</p> <ul style="list-style-type: none"> • VDE approved • Quick lock mechanism for quick and easy blade changeover • Toughened alloy steel blades • Compact fabric storage pouch with integral belt loop 	
--	---

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4915	VDE S/Driver Interchangeable Blade Set	5013969070149	82054000	
T4915M2	VDE S/Driver Blade MOD2	5013969070224	82054000	
T4915PZ0	VDE S/Driver Blade PZ0	5013969070194	82054000	
T4915PZ1	VDE S/Driver Blade PZ1	5013969070200	82054000	
T4915PZ2	VDE S/Driver Blade PZ2	5013969070217	82054000	
T4915S30	VDE S/Driver Blade SL3.0mm	5013969070156	82054000	
T4915S40	VDE S/Driver Blade SL4.0mm	5013969070163	82054000	
T4915S55	VDE S/Driver Blade SL5.5mm	5013969070163	82054000	
T4915S65	VDE S/Driver Blade SL6.5mm	5013969070187	82054000	

<p>Technical product information</p>	<p>Blades</p> <p>SCVM steel blades hardened, tempered and chemically blacked.</p> <p>Contents:</p> <ul style="list-style-type: none"> • 1000V VDE High torque screwdriver handle • 1000V VDE precision screwdriver handle • Slotted 1000V VDE screwdriver blades, sizes: 3.0x100mm, 4.0x100mm, 5.5x100mm, 6.5x100mm • PZ 1000V VDE screwdriver blades, sizes: PZ0x60mm, PZ1x80mm, PZ2x100mm • Modulo 1000V VDE screwdriver blades, size: MOD2 • Fabric storage pouch
--------------------------------------	--

Standards compliance	Electrical safety Fully approved and independently audited by the German VDE to IEC60900 VDE
User health and safety information	Users and bystanders are advised to wear safety goggles. Users are advised to regularly examine their VDE tools, Even the slightest damage can compromise the insulation integrity and potentially expose the user to the risk of injury or even death.
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4915	130	60	170	424	180	60	185	486
T4915M2	10	10	150	30	50	15	200	48
T4915PZ0	10	10	130	15	50	15	200	33
T4915PZ1	10	10	130	18	50	15	200	36
T4915PZ2	10	10	150	30	50	15	200	48
T4915S30	10	10	130	10	50	15	200	28
T4915S40	10	10	140	14	50	15	200	32
T4915S55	10	10	150	20	50	15	200	38
T4915S65	10	10	150	26	50	15	200	44

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4915	-	-	-	-	6	3
T4915M2	22	28	15	2803	8	6
T4915PZ0	22	28	15	2052	8	6
T4915PZ1	22	28	15	2202	8	6
T4915PZ2	22	28	15	2802	8	6
T4915S30	22	28	15	1801	8	6
T4915S40	22	28	15	2002	8	6
T4915S55	22	28	15	2302	8	6
T4915S65	22	28	15	2602	8	6

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4915	-	-	62	Display Box	-	-	-	-
T4915M2	10	Blister	8	Backing Card	-	-	44	Shelf Box
T4915PZ0	10	Blister	8	Backing Card	-	-	44	Shelf Box
T4915PZ1	10	Blister	8	Backing Card	-	-	44	Shelf Box
T4915PZ2	10	Blister	8	Backing Card	-	-	44	Shelf Box
T4915S30	10	Blister	8	Backing Card	-	-	44	Shelf Box
T4915S40	10	Blister	8	Backing Card	-	-	44	Shelf Box
T4915S55	10	Blister	8	Backing Card	-	-	44	Shelf Box
T4915S65	10	Blister	8	Backing Card	-	-	44	Shelf Box