

SportyCam W6

HD Outdoor waterproof Camcorder

120° wide-angle HD outdoor camcorder

5 cm (2.0'') Touch screen user interface

Waterproof diving case (up to 10 m)

Including mounts for bike and helmet



Art- Nr. 400484



**Waterproof
IPX8**



720P HD



**2"
Touch screen**



**5
mega-pixel**



**4X
digital Zoom**

Product Features

SportyCam W6 is a HD outdoor camcorder with an ultra wide-angle lens. Small, light and equipped with chosen hardware, the W6 is suitable for outdoor activities such as diving, climbing, skiing, and biking. Equipped with a nice range of mounting plates and fixing materials the SportyCam W6 can be used for most circumstances. The HD sporty cam records video in 720P high definition quality. With touch screen, it's easy to operate. Enjoy your experiences by connecting the SportyCam W6 to your HDTV over HDMI. SportyCam W6 is the perfect solution for price-conscious outdoor activists.

- HD (1280x720) video recording up to 30 fps
- Support HDTV via HDMI
- External card slot for microSD cards up to 32 GB
- Waterproofed with diving case (up to 3 m)
- Built-in Li-Ion battery for video recoding up to 90 minutes
- Tripod thread on both, camera and underwater case
- Coming with multiple mounting plates for bike and helmet



Helmet Mount



Waterproof Case



Bike Mount

Technical Details

Product Features

Sensor Type	1.3 mega-pixel CMOS sensor
View Angle	120 ° Fixed wide angle
Frame Rate at Video mode	HD: 1280 x 720, 30 fps, 16:9 VGA: 640 x 480, 60 fps, 4:3
Still Image Resolution	5 Mega-pixel (2592 x 1944), interpolated 3.1 Mega-pixel (2048 x 1536), interpolated 1.3 Mega-pixel (1280 x 960)
File format	H.264 (.AVI), JPEG
Display	5 cm (2.0"), touch panel
External Memory	Micro SD / SDHC up to 32 GB
Aperture Range	F3.1
Focal length	f= 9.3 mm
Focus Range	30 cm ~∞
Digital Zoom	4x
Waterproofed	IP X8 (up to 10 m) with additional case
Operation	Touch Screen, On/Off, Shutter Key

Functions

Modes	Photo, Video, Auto
Exposure Control	Auto
White balance	Auto
Internal Mic	Yes
Cycling Recording	Yes, 5 mins /per video clip

Connections

PC Connection	Mini USB (USB 2.0)
HDMI-out	Mini HDMI

Power

Input power supply	DC: 110-240V, 50 / 60Hz
Output power supply	AC: 5V, 1.0 A
Charging time	4 hours

Product Details

Battery	440 mAh, 3.7V, Li-Ion rechargeable battery
Battery Lifetime	90 Minutes
Dimension	66 mm x 43 mm x 27 mm (LxWxH)
Colour	Blue
Weight	48 g
Operating Temperature	To be confirmed
Humidity	To be confirmed
Model Code	W6

Software & System Requirements

OS:	Windows XP SP2 / Vista / 7 / 8
CPU	AMD or Intel CPU with 3.2 GHz or multi core CPU
RAM	1 GB (2 GB recommended)
Other	Graphic card with 256MB memory, 1 free USB port

Package Content

Package Content	SportyCam W6, waterproof case, bike mount, helmet mount, Helmet Belt, USB cable, Quick Start Guide
------------------------	--

Logistic Data

Giftbox Language	EN/DE
Manual Language	EN/DE
Dimension/Giftbox	143×75×255 mm (LxWxH)
Weight/Giftbox	450 g
Pieces/Carton	10 / carton
Dimension/Carton	405 × 265 × 305 mm (LxWxH)
Weight/Carton	5 kg
AIPTEK Art-No.	400484
EAN-Code	4719851877612
Warranty	24 Months in EU

Version: EN 18/02/2014

We reserve the right for technical changes and mistakes

For information about our products concerning § 33 (EC) No. 1907/2006 (REACH) please refer to www.aiptek.eu/reachinfo