


Triple High Definition Tuners - 2 Satellite and 1 Terrestrial/Cable Tuner
Twin Card Readers and RF Modulator
Powered by Spark

Full HD
1080P



S3750CHD



FULL HD TWIN TUNER DVB-S2 RECEIVER AND SINGLE DVB-T2/DVB-C HYBRID TUNER

TWIN CONAX CARD READERS, TWO USBS AND AN RF MODULATOR

DUAL BOOT - SWITCH EASILY BETWEEN SPARK AND E2 LOADER

ETHERNET PORT, WIFI AND 3G MODEM SUPPORT (DONGLE SUPPLIED SEPERATELY)

TIME SHIFTING, RECORDING, PLAYBACK AND MEDIA SUPPORT WITH EXTERNAL HDD (USB 2.0)

HOME NETWORK SUPPORT - SHARE YOUR FILES OVER A LOCAL NETWORK

UNLIMITED NUMBER OF TV AND RADIO CHANNELS SUPPORTED

OPERA WEB BROWSER WITH FLASHLITE

SPARK PORTAL - INCLUDES YOUTUBE, RSS READER, GOOGLE TALK! AND SHOUTCAST FUNCTIONS*



FEATURES

Two Conax Card Readers

Dual Boot - Spark or E2

Unlimited Channels Supported (TV & Radio)

Two High Speed USB Ports (Front and Rear)

Plug In Support

True Colour, User Friendly On Screen Display (OSD)

Timer Support - Set up to Eight Timers

Multiple Sort Types - including FAV, SAT, HD

HbbTV and WebTV (where available)

YouTube, RSS Reader, Spark Portal and Opera Web *

Full 1080P High Definition by HDMI**

Multimedia Playback including MKV, AVI, MPG

Record, Timeshift and Playback with External HDD

EPG Support (Where Broadcast)

Parental Lock

Embedded Games

Digital Audio Output - Coaxial and Optical

File Sharing via Local Network

Alphanumeric Vacuum Fluorescent Display

Ethernet Connection, WiFi and 3G Support

(Icecrypt WiFi Dongle Available separately)

DiSEqC 1.0, 1.1, 1.2 and USALS Compatible

Channel Switching Time <1 Second


SD Output by SCART, RCA or Modulator

Multi Language Support (Menu and OSD)

0.5W Stand-by Power Consumption

*Internet Connection Required/3rd Party Apps subject to change

**HDMI Lead Not Included



SPECIFICATIONS

TUNER & CHANNEL DECODER (SATELLITE - DVB-S2)

Input Connector	FEC Decoder F-type, IEC 169-24, Female
Output Connector	F-type, IEC 169-24, Female
Frequency Range	950MHz ~ 2150MHz
Input Impedance	75Ω, unbalanced
Sensitivity	-65 to -25dBm
LNB Power	13.5/18VDC, max.350mA
22KHz Tone	(22±4)KHz, (0.6±0.2)V
DiSEqC Control	V1.0/1.1/1.2/USALS Compatible
Demodulation	QPSK / 8PSK / 16APSK
Input Symbol Rate	2 ~ 45 Ms/s(QPSK of DVB-S) 2 ~ 45 Ms/s(QPSK of DVB-S2) 2 ~ 45 Ms/s(8PSK of DVB-S2)
FEC Decoder	1/2, 2/3, 3/5, 3/4, 4/5, 5/6, 6/7, 7/8, 8/9 and 8/10 (QPSK) 3/5, 2/3, 3/4, 5/6, 8/9 and 9/10 (8PSK) 2/3, 3/4, 4/5, 5/6, 8/9 and 9/10 (16APSK)

TUNER & CHANNEL DECODER (TERRESTRIAL/CABLE - DVB-T2/DVB-C)

Input Connector	IEC 169-2 Female
Output Connector	IEC 169-2 Male
Frequency Range	VHF L: 51 ~ 142.5 MHz VHF H: 149.5 ~ 426 MHz UHF: 434 ~ 858 MHz
RF Loop In Standby	Active
Demodulation	QPSK / 16QAM / 64QAM / 256QAM
FEC Decoder	1/2, 3/5, 2/3, 3/4, 4/5 and 5/6
Guard Interval	1/4, 1/8, 1/16 and 1/32
Channel Bandwidth	6, 7 and 8 MHz
FFT Mode	2K / 8K

MAIN SYSTEM

Main Processor	ST7162
Memory	RAM : 256 Mbytes FLASH : 512 Mbytes SLC NAND Flash

MPEG TRANSPORT STREAM A/V DECODING

Transport Stream	H.264(MPEG-4 part 10, MPEG-4/AVC and H26L) MPEG-II ISO/IEC 13818-2/11172-2
Profile Level	MPEG-4/AVC MP@L4, MPEG-II MP@HL
Input Rate	Max. 120Mbit/s
Video Formats	4:3 Letter Box, 4:3 PanScan, 16:9
Video Resolution	720 x 576i, 720 x 576p, 720 x 480i, 720 x 480p 1280 x 720p, 1920 x 1080i, 1920 x 1080p
Audio Decoding	Dolby Digital, MPEG-1 Layer 1 and 2, MPEG-2 Layer 2
Audio Mode	Left/Right/Stereo/Mono
Sampling Rate	32KHz, 44.1KHz and 48KHz (According to input)

AUDIO / VIDEO & DATA IN/OUT

RCA	CVBS Video Output, Audio L, R Output
Audio	Digital Coaxial and Optical (S/PDIF)
SCART	TV SCART (CVBS/RGB)
HDMI	Video & Audio Output
USB	USB 2.0 Host Front & Rear Support. (5 Vdc 500 mA max.)
Ethernet	RJ45 connector, 100 Mbps
RF In	IEC 169-2 Female
RF Out (Modulator)	IEC 169-2 Male
RS-232	9 Pin D Type

FRONT PANEL

Slot	2 Smart Card Slots
USB	USB 2.0 Host
Display	Vacuum Fluorescent Display
Buttons	7 Keys (Power, Left, Right, Up, Down, OK, Menu)

POWER SUPPLY

Input Voltage	AC 100-250v, 50/60Hz
Type	SMPS
Power Consumption	Max. 15W
Standby Power	Max. 0.5W

PHYSICAL SPECIFICATION

Size (W x H x D)	300mm X 55mm X 220mm
Weight (Net)	2KG
Operating Temp.	0°C ~ +45°C
Storage Temp.	-10°C ~ +70°C

