

Panel



Screen Size	27"W
Aspect Ratio	16:9
Resolution (max.)	1920x1080
Pixel Pitch (mm)	0.311
Brightness (typ)	300nits
Native Contrast (typ.)	1000:1
DCR (Dynamic Contrast Ratio) (typ.)	12M:1
Panel Type	TN
Viewing Angle (L/R;U/D) (CR>=10)	170°/160°
Response time	2ms (GTG)
Display Colors	16.7million
Color Gamut	72% NTSC

Audio/Video Inputs/Outputs





Input Connector	D-sub / DVI / HDMI / Headphone jack
-----------------	-------------------------------------

Dimensions & Weight



CTN Dimensions (HxWxD mm)	490 x 715 x132
Dimensions(HxWxD mm)	488 x 641 x 215

Dimensions with Wall Mount (HxWxD mm)	N/A
Net Weight (kg)	5.4
Gross Weight (kg)	7.3
Special Features 	
Flicker-free Technology	Yes
Senseye®	Senseye 3
AMA	No
PerfectMotion	No
Windows® 8 Compatible	Yes
Windows® 8.1 Compatible	Yes
HDCP	Yes
Color Temperature	Reddish / Normal/ Bluish / User mode
OSD Language	17 languages
VESA Wall Mounting	100 x100mm
Swivel (left/right)	No
Speaker	No
USB Hub	No
Tilt (down/up)	-5°/20°
Height Adjustment (mm)	No

K Locker	No
Power 	
Power Supply (90~264 AC)	Built-in
Power Consumption (Power saving mode)	<0.3W
Power Consumption (Base on Energy star)	21W