

Verit
VER024922



Verit T85 Wh 113 840 CLA GB

Verit is a versatile and flexible task light. The shade can be adjusted and set to almost any position. A high-frequency electronic ballast offers flicker-free illumination. The spring balanced arm ensures that the head will remain parallel to the work surface, and provides for easy movement.



Electrical data

Voltage from (V)	230
Maximum voltage (V)	240
Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Total consumption (W)	15

Technical data

Maximum ambient temperature (°C)	25
IP classification	20

Body

Colour of body	White
Body material	Steel

Light source

Lamp power (W)	13
Number of lamps	1
Lamp base	G24q-1
Light source	TC-DE

Dimensions

Net weight (kg)	1,4
Arm length (cm)	85

Optic

Lightdistribution Up/Down	0/100
---------------------------	-------

Verit
VER024922



Verit T85 Wh 113 840 CLA GB

Verit is a versatile and flexible task light. The shade can be adjusted and set to almost any position. A high-frequency electronic ballast offers flicker-free illumination. The spring balanced arm ensures that the head will remain parallel to the work surface, and provides for easy movement.



Drawings

