

World's first Thunderbolt™ storage solution

Buffalo Technology's MiniStation Thunderbolt™ Portable HDD is world's first portable Thunderbolt™ with an USB 3.0 dual-interface external drive solution. The Thunderbolt™ (10 GBps) Interface is twice as fast than USB 3.0 while preserving backward compatibility with existing devices that support USB 2.0 or USB 3.0.

The MiniStation Thunderbolt™ Portable HDD can be formatted to support both PC and Mac® making it a great portable storage solution for any device. Native compatibility with Mac OS X Time Machine also makes it an ideal solution for backup with Mac computers.

Bus-powered, the MiniStation Thunderbolt™ Portable HDD requires no additional power supply and is easy to carry. Just plug the portable HDD body with the included Thunderbolt Cable* onto your Mac. Enclosed in a sleek aluminum body with a transparent frosted top, the design feels luxurious. MiniStation Thunderbolt™ Portable HDD features an indirect disk access LED indicator on the underside that tastefully illuminates its supporting surface.

With the MiniStation Thunderbolt™ Portable HDD on the move, you can transfer digital content faster, simplify connections between devices, maintain compatibility with most devices and enjoy the ultra-fast speeds of the market's latest portable storage solution.

* No AC adapter is required



Features and Benefits

- Ultimate speed – Thunderbolt (10 GBps) Interface. Two times faster Interface speed than USB 3.0
- Dual-interface - Thunderbolt and USB 3.0 for the best possible speeds
- Cables included – Thunderbolt and USB 3.0 cables in the box
- Bus powered – No additional power input required
- Apple friendly – Ready for use for Mac immediately and works for Mac Time Machine (HFS+ formatted)
- Design – Sophisticated design



Specifications

Internal Hard Drives	
HDD interface	SATA
Capacities	1TB, 2TB
Interfaces	
Thunderbolt	
Standard compliance	Thunderbolt
Connector type	Thunderbolt (Mini DisplayPort)
Number of ports	1
Data transfer rate	10 GBps
USB	
Standard compliance	USB 3.0
Connector type	Micro-B
Number of ports	1
Data transfer rate	5 GBps
Other	
Supported OS	Thunderbolt - Mac OS® X 10.6 or later USB - Mac OS® X 10.5 or later, Windows® 7 (64-bit/32-bit) / Vista (64-bit/32-bit) / XP (32-bit)
Dimensions (WxDxH)	80.5 × 130 × 22.5 mm
Weight	260 g
Operating environment	5-35°C, 20-80% (Non-Condensing)
Power supply	Bus powered

Product codes

HD-PA1.0TU3-EU

HD-PA2.0TU3-EU

About Buffalo

Buffalo Technology is a leading global provider of award-winning storage, networking and multimedia solutions for the home and small business environments as well as for system builders and integrators. With more than three decades of networking and computer peripheral experience, Buffalo has proven its commitment to delivering innovative solutions that have put the company at the forefront of infrastructure technology.

© Buffalo Inc. 2014. BUFFALO logo, AirStation, Nfiniti, AOSS, TeraStation, LinkStation, DriveStation and MiniStation are either trademarks or registered trademarks of Melco Holdings Inc. or Buffalo Inc. Microsoft Windows and Microsoft logo are either registered trademarks or trademarks of Microsoft Corporation in United States and/or other countries. The names and logos of other companies mentioned herein belong to their respective owners. The information within this datasheet is subject to change without notice. All rights reserved. E & OE.