

2FRP9C



Article Number: 161-05030

Spiralwrap, 1/4" Diameter, PE-FR, Natural, 100ft/RL



Download spec sheet

Base Data

Local Order Number 2FRP9C

Type 2FRP

Color Natural (NA)

- Features and Benefits**
- Sheathing allows flexible routing and lead-out of cables
 - The inner edges are beveled preventing damage to cables
 - Sheathing is reusable and resistant to most chemicals
 - Spiralwrap is U.L. Recognized

Product Description HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Short Description Spiralwrap, 1/4" Diameter, PE-FR, Natural, 100ft/RL

Product Dimensions

Length L (Imperial) 100.0 ft

Length L (Metric) 30.48 m

Reel Length (imperial) 100.0 ft

Variant Spiral Binding

Bundle Diameter Min. (Imperial) 0.18 "

Bundle Diameter Min. (Metric) 4.75 mm

Bundle Diameter Max. (Imperial) 2.0 "

Bundle Diameter Max. (Metric) 50.8 mm

Diameter D (imperial) 0.25 "

Diameter D (metric) 6.35 mm

Nominal Diameter (Imperial) 1/4 "

Nominal Diameter (Metric) 6.35 mm

Wall Thickness WT (Imperial) 0.045 "

Wall Thickness WT (Metric) 1.14 mm

Pitch (imperial) 0.375 "

Pitch (metric) 9.53 mm

Logistics and Packaging

Quantity Per reel

Package Quantity 100.0 ft

Package Quantity (Metric) 30.48 m

Carton Quantity 3000.0 ft

Material and Specifications

Material	Polyethylene, flame retardant (PE-FR)
Material Shortcut	PE-FR
Flammability	UL94 V0
Operating Temperature	-4°F to +176°F (-20°C to +80°C)
ROHS Compliant	Yes
UL Recognized (US)	Yes