

## 3FRP9C



**Article Number:** 161-05049

**Spiralwrap, 1/2" Diameter, PE-FR, Natural, 100ft/RL**



Download spec sheet

### Base Data

**Local Order Number** 3FRP9C

**Type** 3FRP

**Color** Natural (NA)

- Features and Benefits**
- Sheathing allows flexible routing and lead-out of cables
  - The inner edges are beveled preventing damage to cables
  - Sheathing is reusable and resistant to most chemicals
  - Spiralwrap is U.L. Recognized

**Product Description** HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

**Short Description** Spiralwrap, 1/2" Diameter, PE-FR, Natural, 100ft/RL

### Product Dimensions

**Length L (Imperial)** 100.0 ft

**Length L (Metric)** 30.48 m

**Reel Length (imperial)** 100.0 ft

**Variant** Spiral Binding

**Bundle Diameter Min. (Imperial)** 0.37 "

**Bundle Diameter Min. (Metric)** 9.52 mm

**Bundle Diameter Max. (Imperial)** 4.0 "

**Bundle Diameter Max. (Metric)** 102.0 mm

**Diameter D (imperial)** 0.5 "

**Diameter D (metric)** 12.7 mm

**Nominal Diameter (Imperial)** 1/2 "

**Nominal Diameter (Metric)** 12.7 mm

**Wall Thickness WT (Imperial)** 0.062 "

**Wall Thickness WT (Metric)** 1.57 mm

**Pitch (imperial)** 0.56 "

**Pitch (metric)** 14.3 mm

### Logistics and Packaging

**Quantity Per** reel

**Package Quantity** 100.0 ft

**Package Quantity (Metric)** 30.48 m

**Carton Quantity** 1200.0 ft

## Material and Specifications

---

<b>Material</b>	Polyethylene, flame retardant (PE-FR)
<b>Material Shortcut</b>	PE-FR
<b>Flammability</b>	UL94 V2
<b>Operating Temperature</b>	-4°F to +176°F (-20°C to +80°C)
<b>ROHS Compliant</b>	Yes
<b>UL Recognized (US)</b>	Yes