

5NFP0C



Article Number: 161-05079

Spiralwrap, 1" Diameter, PE, Black, 100ft/RL



[Download spec sheet](#)

Base Data

Local Order Number 5NFP0C

Type 5NFP

Color Black (BK)

- Features and Benefits**
- Sheathing allows flexible routing and lead-out of cables
 - The inner edges are beveled preventing damage to cables
 - Sheathing is reusable and resistant to most chemicals
 - Spiralwrap is U.L. Recognized

Product Description HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Short Description Spiralwrap, 1" Diameter, PE, Black, 100ft/RL

Product Dimensions

Length L (Imperial) 100.0 ft

Length L (Metric) 30.48 m

Reel Length (imperial) 100.0 ft

Variant Spiral Binding

Bundle Diameter Min. (Imperial) 1.0 "

Bundle Diameter Min. (Metric) 25.4 mm

Bundle Diameter Max. (Imperial) 7.0 "

Bundle Diameter Max. (Metric) 178.0 mm

Diameter D (imperial) 1.0 "

Diameter D (metric) 25.4 mm

Nominal Diameter (Imperial) 1 "

Nominal Diameter (Metric) 25.4 mm

Wall Thickness WT (Imperial) 0.095 "

Wall Thickness WT (Metric) 2.41 mm

Pitch (imperial) 1.0 "

Pitch (metric) 25.4 mm

Logistics and Packaging

Quantity Per reel

Package Quantity 100.0 ft

Package Quantity (Metric) 30.48 m

Carton Quantity 300.0 ft

Material and Specifications

Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	Flammable
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
ROHS Compliant	Yes
UL Recognized (US)	Yes