

## NC60



Article Number: 148-00009

Nail Clip, .24" Cable Diameter, PP;ST, Black, 100/pkg



Download spec sheet

### Base Data

Local Order Number NC60

Type NC6

Color Black (BK)

**Features and Benefits**

- Hardened steel nail allows easy installation into wood, masonry joints, cinder block and mortar.
- No sharp edges reduce risk of cutting cables or sheaths.

**Product Description** HellermannTyton tough, precision engineered nail clips hold wire and cable securely in place. The nail is made of hardened steel for driving into wood, masonry joints, cinder block and mortar. The nail clips do not have sharp edges, which reduce the chance of cutting cable jackets or sheaths, causing signal loss. Available in white or black.

**Short Description** Nail Clip, .24" Cable Diameter, PP;ST, Black, 100/pkg

### Product Dimensions

Length L (Imperial) 0.63 "

Length L (Metric) 16.0 mm

Width W (Imperial) 0.49 "

Width W (Metric) 12.5 mm

Width W2 (Imperial) 0.26 "

Width W2 (Metric) 6.5 mm

Height H (Imperial) 0.32 "

Height H (Metric) 8.0 mm

Nominal Diameter (Imperial) 1/4 "

Nominal Diameter (Metric) 6.0 mm

### Logistics and Packaging

Quantity Per box

Package Quantity (Metric) 100 Pieces

Carton Quantity 20000

### Material and Specifications

Material Polyethylene (PE)

Material Shortcut PE

Flammability UL94 HB

Operating Temperature -40°F to +239°F (-40°C to +115°C)

ROHS Compliant Yes

