

## PBM0C2



**Article Number:** 151-00228

**Push Mount, .25" Hole Dia., .12" Max Panel, .2" Max Tie Width, PA66, Black, 100/pkg**



Download spec sheet

### Base Data

<b>Local Order Number</b>	PBM0C2
<b>Type</b>	PBM
<b>Color</b>	Black (BK)
<b>Features and Benefits</b>	<ul style="list-style-type: none"> <li>• Push Mounts, when used with standard cable ties, provide a permanent bundling solution below a panel.</li> <li>• The "button" style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.</li> </ul>
<b>Product Description</b>	HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas.
<b>Short Description</b>	Push Mount, .25" Hole Dia., .12" Max Panel, .2" Max Tie Width, PA66, Black, 100/pkg

### Product Dimensions

<b>Width W (Imperial)</b>	0.26 "
<b>Width W (Metric)</b>	6.6 mm
<b>Cable Tie Width Max. (Imperial)</b>	0.2 "
<b>Cable Tie Width Max. (Metric)</b>	5.0 mm
<b>Height H (Imperial)</b>	0.4 "
<b>Height H (Metric)</b>	10.2 mm
<b>Height H2 (Imperial)</b>	0.08 "
<b>Height H2 (Metric)</b>	2.0 mm
<b>Panel Thickness Max. (Imperial)</b>	0.12 "
<b>Panel Thickness Max. (Metric)</b>	3.0 mm
<b>Mounting Hole Diameter D (Imperial)</b>	0.25 "
<b>Mounting Hole Diameter D (Metric)</b>	6.35 mm
<b>Mounting Hole Diameter D Max. (Imperial)</b>	0.29 "
<b>Mounting Hole Diameter D Max. (Metric)</b>	6.4 mm
<b>Mounting Hole Diameter D Min. (Metric)</b>	6.35 mm

### Logistics and Packaging

<b>Quantity Per</b>	bag
<b>Package Quantity (Metric)</b>	100
<b>Carton Quantity</b>	15000

### Material and Specifications

**Material** Polyamide 6.6 (PA66)

**Material Shortcut** PA66

**Flammability** UL94 V2

**Operating Temperature** -40°F to +185°F (-40°C to +85°C)

**ROHS Compliant** Yes

**Certification/Specification** UL

**UL Listed (US and Canada)** No

**UL Recognized (US and Canada)** Yes