

SRCI0500C2



Article Number: 151-00278

TSR Adhesive Cable Clamp, .76" Width, .51" Height, PVC, Ivory, 100/pkg



Download spec sheet

Base Data

Local Order Number SRCI0500C2

Type SRCI0500

Color Ivory (IV)

Features and Benefits

- Co-extruded hinge offers unlimited access to wire and cables and can be open and closed repeatedly without signs of wear.
- Rubber based adhesive allows for a permanent bond to most surfaces.

Product Description Manufactured from HellermannTyton's surface raceway, these adhesive cable clamps are designed with a co-extruded hinge offering unlimited and easy access to wire and cable. The clip can be open and closed repeatedly without deformation or signs of wear. The rubber based adhesive allows for a permanent bond to most surfaces. Available in three sizes.

Short Description TSR Adhesive Cable Clamp, .76" Width, .51" Height, PVC, Ivory, 100/pkg

Product Dimensions

Length L (Imperial) 0.75 "

Length L (Metric) 19.1 mm

Width W (Imperial) 0.84 "

Width W (Metric) 21.3 mm

Width W2 (Imperial) 0.76 "

Width W2 (Metric) 19.3 mm

Height H (Imperial) 0.51 "

Height H (Metric) 13.0 mm

Bundle Diameter Max. (Imperial) 0.5 "

Bundle Diameter Max. (Metric) 12.7 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100 Pieces

Material and Specifications

Material Polyvinylchloride (PVC)

Material Shortcut PVC

Adhesive Rubber

Flammability UL94 V0 (excluding adhesive)

Operating Temperature +122°F (+50°C)

ROHS Compliant Yes

© HellemannTyton 2015