

T50ML0C2



Article Number: 113-00007

Screw Mount Tie, 50lb, 15.4", Max Bundle Diameter 4.0", #10 Screw, PA66, Black, 100/pkg



Download spec sheet

Base Data

Local Order Number	T50ML0C2
Type	T50ML
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"> • Mount design secures firmly with any #10 Screw. • Screw mount style creates low insertion and high extraction force.
Product Description	Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.
Short Description	Screw Mount Tie, 50lb, 15.4", Max Bundle Diameter 4.0", #10 Screw, PA66, Black, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	50.0 lbs
Minimum Tensile Strength (Metric)	225 N
Length L (Imperial)	15.4 "
Length L (Metric)	390.0 mm
Fixation Method	fixing hole
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18 "
Width W (Metric)	4.7 mm
Height H (Imperial)	0.23 "
Height H (Metric)	5.7 mm
Bundle Diameter Min. (Imperial)	0.12 "
Bundle Diameter Min. (Metric)	3.0 mm
Bundle Diameter Max. (Imperial)	4.0 "
Bundle Diameter Max. (Metric)	100.0 mm
Mounting Hole Diameter D (Imperial)	0.22 "
Mounting Hole Diameter D (Metric)	5.5 mm
Mounting Hole Diameter D Max. (Metric)	5.5 mm
Mounting Hole Diameter D Min. (Metric)	5.5 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 5000

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL94 V2

Operating Temperature -40°F to +221°F (-40°C to +105°C)

ROHS Compliant Yes

Certification/Specification UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) Yes