

TM1SF10C2



Article Number: 151-40119

Push Mount, .25" Hole Dia., .13" Max Panel, .2" Max Tie Width, PA66, White, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number TM1SF10C2

Type TM1SF

Color White (WH)

Features and Benefits

- Push Mounts, when used with standard cable ties, provide a permanent bundling solution.
- The low profile style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.

Product Description HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for quick installation by pushing the mount through a pre-drilled hole. The low profile head is suitable in space constrained areas.

Short Description Push Mount, .25" Hole Dia., .13" Max Panel, .2" Max Tie Width, PA66, White, 100/pkg

Product Dimensions

Length L (Imperial) 0.62 "

Length L (Metric) 15.8 mm

Fixation Method with Arrowhead / Push Mount (Mounts)

Width W (Imperial) 0.4 "

Width W (Metric) 10.2 mm

Cable Tie Width Max. (Imperial) 0.2 "

Cable Tie Width Max. (Metric) 5.0 mm

Height H (Imperial) 0.18 "

Height H (Metric) 4.6 mm

Height H2 (Imperial) 0.18 "

Height H2 (Metric) 4.6 mm

Panel Thickness Max. (Imperial) 0.13 "

Panel Thickness Max. (Metric) 3.40 mm

Panel Thickness Min. (Imperial) 0.13 "

Panel Thickness Min. (Metric) 3.30 mm

Mounting Hole Diameter D (Imperial) 0.25 "

Mounting Hole Diameter D (Metric) 6.35 mm

Mounting Hole Diameter D Max. (Imperial) 0.28 "

Mounting Hole Diameter D Max. (Metric) 6.35 mm

Mounting Hole Diameter D Min. (Metric) 6.35 mm

Logistics and Packaging

Quantity Per pieces

Package Quantity (Metric) 100 Pieces
Carton Quantity 15000 Pieces
Weight (Metric) 1 kg

Material and Specifications

Material Polyamide 6.6 (PA66)
Material Shortcut PA66
Flammability UL94 V2
Operating Temperature -40°F to +185°F (-40°C to +85°C)
ROHS Compliant Yes
UL Listed (US and Canada) No
UL Recognized (US and Canada) Yes