




1/4"

carolus



- 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
- 3 - 4 - 5 - 6 - 8 - 10 mm
- 50 / 100 mm
- 1/4" ■ x 1/4" ●


1/4"	6,3	Code	Art.-No.	mm	g
		1514326	4004.79	200 x 110 x 30	1080



5°
72 Zähne/Teeth


- 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
- 3 - 4 - 5 - 6 - 8 - 10 mm
- 50 / 100 mm
- 1/4" ■ x 1/4" ●

1/4"	6,3	Code	Art.-No.	mm	g
		1514512	4004.99	200 x 110 x 30	1080



- 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
- 3 - 4 - 5 - 6 - 8 - 10 mm
- 50 / 100 mm
- 8 mm x 1/4" $\ominus 2,5 / 3,5$
- 1/4" ■ x 1/4" ●

1/4"	6,3	Code	Art.-No.	mm	g
		1695959	4004.49	200 x 110 x 30	1080



5°
72 Zähne/Teeth

- 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
- 3 - 4 - 5 - 6 - 8 - 10 mm
- 50 / 100 mm
- 8 mm x 1/4" $\ominus 2,5 / 3,5$
- 1/4" ■ x 1/4" ●

1/4"	6,3	Code	Art.-No.	mm	g
		1695975	4004.59	200 x 110 x 30	1080

4004.79
4004.99



4004.49
4004.59



PH 0 / 1 2,5 / 3,5 mm