




1/4"


carolus




- 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
- 3 - 4 - 5 - 6 - 8 - 10 mm
- 50 / 100 mm
- 8 mm x 1/4"




1/4"	6.3	Code	Art.-No.	mm	kg
		1514407	4004.86	200 x 110 x 30	1100




- 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
- 3 - 4 - 5 - 6 - 8 - 10 mm
- 50 / 100 mm
- 8 mm x 1/4"




1/4"	6.3	Code	Art.-No.	mm	kg
		1514458	4004.91	200 x 110 x 30	1100




- 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
- 3 - 4 - 5 - 6 - 8 - 10 mm
- 50 / 100 mm
- 8 mm x 1/4"



1/4"	6.3	Code	Art.-No.	mm	kg
		1514350	4004.81	200 x 110 x 30	1100



- 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- TX10 - TX15 - TX20 - TX25 - TX27 - TX30 - TX40
- 3 - 4 - 5 - 6 - 8 - 10 mm
- 50 / 100 mm
- 8 mm x 1/4"



1/4"	6.3	Code	Art.-No.	mm	kg
		1514369	4004.81tk	200 x 110 x 30	1100

