

DI Boxes

ULTRA-DI DI20

Professional Active 2-Channel
DI-Box/Splitter

- Professional and multi-purpose direct injection box for stage and studio applications
- Provides impedance and signal matching for the direct connection of instruments to mixers and amplifiers
- Converts 2 independent unbalanced ¼" TRS line inputs into 2 balanced XLR outputs
- Additional Split mode (channel 1 assigns signal to both XLR outputs)
- Ultra-flat frequency response due to servo-balanced operation
- Internal battery automatically shuts off when phantom power is applied
- Allows direct connection to speaker outputs with up to 3,000 Watts
- Ground Lift switch eliminates typical ground loop problems
- Input 2 usable as channel 1 Link output (additional to XLR output)
- ¼" TRS and gold-plated XLR connectors
- Ultra-rugged, road-suitable metal case
- High-quality components and exceptionally rugged construction ensure long life
- Conceived and designed by BEHRINGER Germany



The ULTRA-DI DI20 is a one-of-a-kind DI (Direct Injection) box that can convert up to two separate, unbalanced ¼" TRS lines into two balanced XLR outputs – or function as a signal splitter. Electric guitarists, keyboardists and bassists will love the flexibility the incredible DI20 provides both in the studio and on the stage.



Mono, Stereo or Double the Amps

By flipping a switch, you can use the DI20 as a launching pad for two separate mono signals, a stereo signal – or a split-signal feeding two separate amps. The DI20 also features a superb ground-lift switch, and the 3-position input attenuator can accommodate input levels of up to +48 dBu. This handy built-in attenuator also allows you to connect directly to your amplifier's speaker outputs, even amps rated as high as 3,000 Watts. You can power the DI20 with either a 9 V battery or your mixer's phantom power supply (+18 to +48 V DC). The whole package is wrapped in an ultra compact, road-suitable and rugged metal housing.

DI Boxes

ULTRA-DI DI20

Professional Active 2-Channel
DI-Box/Splitter

Be Direct

If you're a working musician who demands uncompromising functionality and durability, the ULTRA-DI DI20 will astound you – and so will its ultra-affordable price tag! See what the DI20 can do for your sound at your nearest [BEHRINGER](#) dealer – or get yours online today.



You Are Covered

We always strive to provide the best possible Customer Experience. Our products are made in our own **MUSIC Group** factory using state-of-the-art automation, enhanced production workflows and quality assurance labs with the most sophisticated test equipment available in the world. As a result, we have one of the lowest product failure rates in the industry, and we confidently back it up with a generous **3-Year Warranty** program.

DI Boxes

ULTRA-DI DI20

Professional Active 2-Channel
DI-Box/Splitter



DI Boxes

ULTRA-DI DI20

Professional Active 2-Channel
DI-Box/Splitter



For service, support or more information contact the BEHRINGER location nearest you:

Europe
MUSIC Group Services UK
 Tel: +44 156 273 2290
 Email: CARE@music-group.com

USA/Canada
MUSIC Group Services NV Inc.
 Tel: +1 702 800 8290
 Email: CARE@music-group.com

Japan
MUSIC Group Services JP K.K.
 Tel: +81 3 6231 0454
 Email: CARE@music-group.com

MUSIC Group accepts no liability for any loss which may be suffered by any person who relies either wholly or in part upon any description, photograph, or statement contained herein. Technical specifications, appearances and other information are subject to change without notice. All trademarks are the property of their respective owners. MIDAS, KLARK TEKNIK, TURBOSOUND, BEHRINGER, BUGERA and DDA are trademarks or registered trademarks of MUSIC Group IP Ltd. © MUSIC Group IP Ltd. 2015 All rights reserved.

