


## LC-plus 280



white





### **i** PRODUCT INFORMATION

- Motion detector with 360° creep zone for gapless coverage
- Adjustable ball head
- Detection area can be restricted with blinds
- Special socket for external corner mounting included
- Simple socket mounting

### ■ TECHNICAL DATA

- 110-240 V AC , 50 / 60 Hz
- 280°
- max. 16 m when walking across (tangential)
- IP44 / Class II
- 25°C to +50°C
- Housing UV- and shock resistant polycarbonate
- IR-LC-plus, IR-LC-Mini
- Channel 1 (control the lighting)**
- 2000 W,  $\cos \varphi = 1$   
1000 VA,  $\cos \varphi = 0.5$
- 15 s - 16 min or pulse
- 10 - 2000 Lux



Description	Colour	Part number
LC-plus 280	white	91008
LC-plus 280	brown	91018
LC-plus 280	black	91028
LC-plus 280	silver	91048
<b>Accessory (optional)</b>		
IR-LC-Mini	grey	92093
IR-LC-plus	grey	92095
Wire basket BSK (Ø 164 x 143)	white	92467