

General Information

Manufacturer:	Acer, Inc
Manufacturer Part Number:	UM.FV6EE.026
Manufacturer Website Address:	http://www.acer.co.uk
Brand Name:	Acer
Product Series:	V
Product Model:	V246HL
Product Name:	V246HL Widescreen LCD Monitor
Product Type:	LCD Monitor

Additional Product Specifications

Full Product Specifications: [Click to view](#)

Technical Information

Number of Screens:	1
Screen Size:	61 cm (24")
Screen Mode:	Full HD
Panel Technology:	Twisted Nematic Film (TN Film)
Response Time:	5 ms
Aspect Ratio:	16:9
Backlight Technology:	LED
Maximum Adjustable Height:	No
Tilt Angle:	-5°to25°
Swivel Angle:	No

Video

Maximum Resolution:	1920 x 1080
Colour Support:	16.7 Million Colours
Contrast Ratio:	100,000,000:1
Brightness:	250 cd/m ²

Interfaces/Ports

DVI:	Yes
HDMI:	Yes

VGA:	Yes
Power Description	
Operating Power Consumption:	20.90 W
Standby Power Consumption:	450 mW
Off-Mode Power Consumption:	350 mW
Operating Power Consumption (Energy Star):	20.90 W
Physical Characteristics	
Colour:	Black
Height:	335.9 mm
Width:	567 mm
Depth:	52 mm
Height with Stand:	422.20 mm
Width with Stand:	567 mm
Depth with Stand:	206.80 mm
Weight (Approximate):	3.50 kg
Weight with Stand (Approximate):	3.90 kg
Miscellaneous	
Package Contents:	<ul style="list-style-type: none">• V246HL Widescreen LCD Monitor• Power Cord• 1 x VGA Cable
Green Compliant:	Yes
Green Compliance Certificate/Authority:	TCO Certified Displays 6.0
Warranty	
Limited Warranty:	3 Year