

# HANNspree

## HANNSpad8"HD 3G


Android Tablet 20,32 cm



ANDROID

4.4 KitKat

3G+  
DATA




- CPU High Performance Quad-Core / ARM Cortex 1.3Ghz
- 3G Modem Built-in
- GPS function
- Android 4.4
- 8" IPS LED Backlight Panel
- 1280 x 800 HD Resolution
- 8Gb Storage Memory
- Dual Camera 0.3MP/ 2MP Auto-Focus
- Super Sim design / Brushed metal finish casing



Multitouch Screen



8" Panel




Micro SD  
card slot



1280x800  
Resolution




0.3MP Front  
2MP Rear



Quad  
Core  
1.3GHz



OTA



3G+  
Data



Low Power  
Consumption



8GB  
storage capacity



RAM  
1GB



4.4  
Powered by  
Android

# Ultra-Mobile Tablet PC | EU

SN80W71

# HANNspree

Brand	Hannspree
Model	SN80W71
Screen	8 inch , 16:10, 1280x800 (IPS)
Touchscreen Type	Multi touch screen
View Angle	Horizontal: 178° / Vertical: 178°
Processor	MTK8382 Quadcore 1.3G cortex-A7,
Quad Core Memory	1GB DDR3
Storage Internal	8GB NAND FLASH
Storage External	TF Micro-SD Card-Reader, Max.32GB
WLAN	WLAN 802.11 b/g/n
Bluetooth	BT4.0
Camera	Dual-Camera – Front:0.3 MP / Rear:2 MP
Microphone	Built-in
Speakers output	1x1W
Headphones output	D3.5 mm Stero earphone support phone calling
2G/3G	WCDMA/HSDPA/HSUPA: 900 MHz /2100 MHz GSM/GPRS/EDGE: 850MHz/900 MHz/1800 MHz/1900 MHz
Data Transmission	(TBC)
GPS	Yes
Sim-Card	Yes
G Sensor	√
3 axis Accelerometer	√
Battery Type	4000mAh
Battery Life	Standby: 300 Hours / Internet Browsing (w WiFi) 3 hours 55 Minutes / Video Playback 4 hours 39 minutes (100% Brightness 720p)
Power Adapter	AC 100V~240V , Micro USB 5V/2A
Operating Temperature	0 to 50°C
Operating Humidity	10~90%
Case Material	Metal + Plastic (PET) material for back cover
Dimension (W*D*H mm)	213*134*8.6 mm
Packing dimension (W*D*H mm)	247*201*50mm

Packaging	Color carton
Net weight	386g
Gross weight	677g
Keys	Power, Volume +/-
Operating System	Android 4.4.2 and above
Software App	Browser, Calculator, Calendar, Camera, Clock, Demo, Downloads, Email, Gallery, Google, HSP Explorer, Music, Play Store, Settings, Sound Recorder, Voice Search
Supported Audio Formats	MP3, MIDI, WAV, PCM, OGG
Supported Image Formats	JPG, BMP, PNG, OGG
Miracast	Support 720P
User manual	Multi-Language PDF (EN, IT, GE, FR)
Accessory	1 adaptor with 2 clips and 1 USB cable
Certification	EU: CEEMC, CER&TTE, CB, ErP, RoHS, REACH, WEEE

[www.hannspree.eu](http://www.hannspree.eu)

Actual products may differ slightly from those illustrated on this promotion material. Please refer to actual samples for final selection. The products displayed on this promotion material may not be available for purchase in your particular country or locality. Please check with your local authorized representatives for the availability of specific products in your area. Hannspree reserves the right to alter