



4-50
HOURS
RUNTIME

250
METRE
BEAM RANGE

900
LUMENS
OUTPUT

IPX7
WATER
PROOF



2-30
HOURS
RUNTIME

175
METRE
BEAM RANGE

350
LUMENS
OUTPUT

IPX7
WATER
PROOF

LIGHT BY
CREE 
LEDs

USB
CHARGING

- » **HV-FL9R** 900 Lumen white CREE LED
- » **HV-FL7R** 350 Lumen white CREE LED
- » Built in USB rubberised charging point with Micro-USB cable (included)
- » Hard anodized die cast matte aluminium body
- » Tactical rubberised micro switch operation
- » 3 light mode settings and 8Hz defence strobe
- » Water resistant IPX7 - 1M submersible
- » Impact resistant to 1M
- » Nylon velcro holster (included)
- » Safety nylon wrist strap (included)

HV-FL9R

BATTERY 3.7v 2600 mAh 18650 Li-ion Battery (inc)
WEIGHT 200g with battery
DIMENSION 139 x 33mm

HV-FL7R

BATTERY 3.7v 600 mAh 14430 Li-ion Battery (inc)
WEIGHT 124g with battery
DIMENSION 117 x 29mm



POUCH AND USB CABLE (INC)



ALUMINIUM HOUSING



RECHARGEABLE BATTERY (INC)



USB RECHARGEABLE