

# HIVIS RUBBER WEATHERPROOF LED LANTERN



**BEAMASTER**  
LENS

10 HOURS RUNTIME	190 METRE BEAM RANGE	200 LUMENS OUTPUT	IP54 DUST+WATER RESISTANCE
------------------------	----------------------------	-------------------------	----------------------------------



EASY PUSH BUTTON  
MICRO SWITCH



REAR CHARGING POINT



OPTICAL BEAMMASTER LENS



WEATHERPROOF

- » 200 Lumen white Seoul LED
- » Synthetic industrial grade rubber housing
- » Rear charging point for use with rechargeable batteries
- » Floats beam upright in water
- » Ultra tough polycarbonate reflector
- » Optical Beammaster lens for beam penetration
- » Contoured rubber easy grip handle
- » Rubber moulded push micro switch
- » Highly robust build quality

<b>BATTERY</b>	1 x 6v PJ996 Battery (not included)
<b>WEIGHT</b>	960g (with battery)
<b>DIMENSION</b>	180 x 110mm

# HIVIS RUBBER WEATHERPROOF LED LANTERN



**BEAMASTER**  
LENS

10  
HOURS  
RUNTIME

250  
METRE  
BEAM RANGE

300  
LUMENS  
OUTPUT

IP54  
DUST+WATER  
RESISTANCE



EASY PUSH BUTTON  
MICRO SWITCH



REAR CHARGING POINT



OPTICAL BEAMASTER LENS



WEATHERPROOF

- » 300 Lumen white Seoul LED
- » Synthetic industrial grade rubber housing
- » Rear charging point for use with rechargeable batteries
- » Floats beam upright in water
- » Ultra tough polycarbonate reflector
- » Optical Beamaster lens for beam penetration
- » Contoured rubber easy grip handle
- » Rubber moulded push micro switch
- » Highly robust build quality

**BATTERY** 1 x 6v PJ996 Battery (not included)  
**WEIGHT** 960g (with battery)  
**DIMENSION** 180 x 110mm