

CTAM110C2



Article Number: 151-31109

Cable Tie Anchor Mount, 0.17" Hole Dia., 0.2" Max Tie Width, PA66, White, 100/pkg



Download spec sheet

Base Data

Local Order Number CTAM110C2

Type CTAM1

Color White (WH)

Features and Benefits

- 4-way entry allowing the cable tie to secure bundles running parallel or perpendicular.
- Secures with a single screw providing quick installation.

Product Description HellermannTyton cable tie anchor mounts are designed with a 4-way entry allowing the cable tie to secure bundles running parallel or perpendicular. The mounts are installed quick and easy by securing a single screw.

Short Description Cable Tie Anchor Mount, 0.17" Hole Dia., 0.2" Max Tie Width, PA66, White, 100/pkg

Product Dimensions

Length L (Imperial) 0.8 "

Length L (Metric) 20.4 mm

Fixation Method Screw Mounting and Rivet

Width W (Imperial) 0.4 "

Width W (Metric) 10.2 mm

Cable Tie Width Max. (Imperial) 0.2 "

Cable Tie Width Max. (Metric) 5.0 mm

Height H (Imperial) 0.2 "

Height H (Metric) 5.1 mm

Height H2 (Imperial) 0.06 "

Height H2 (Metric) 1.8 mm

Mounting Hole Diameter D (Imperial) 0.17 "

Mounting Hole Diameter D (Metric) 4.3 mm

Mounting Hole Diameter D Max. 4.3 mm

(Metric) **Mounting Hole Diameter D Min. (Metric)** 4.3 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100 Pieces

Carton Quantity 15000

Weight (Metric) 2 kg

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL94 V2

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

Certification/Specification UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) Yes