



Features:

- Universal / Full Range Input
- Interchangeable AC Heads
- Level 6 Efficiency
- Cost Effective & Highly Reliable
- 1 Year Warranty



Characteristics		
Part Number	T58665T	T58485T
Output Voltage	5V	5V
Output Current Max	1A	2A
Output Current Min	0A	0A
Power (Watts)	5W	10W
Output Regulation	+/-5%	
Ripple & Noise (mV p-p)	300 (mV p-p)	300 (mV p-p)
Protections	Over Current Short Circuit Over Current	
Rated Input Voltage	100 - 240 Vac	
Full Input Voltage Range	90 - 264Vac	
Rated Frequency	50 / 60 Hz	
Full Frequency Range	47 / 63Hz	
Efficiency	79%	79%
Input Current (RMS Max)	0.3A	
Inrush Current	No Damage	
Turn on Delay	3 Seconds Max.	
AC Inlet	Interchangeable UK, Euro, US & Aus Plugtop	
DC Outlet	5Vdc USB Outlet	
Operating Temperature	0 to 40C	
Storage Temperature	-20 to 60C	
Operating Humidity	20 - 85%	
Storage Humidity	5 - 95%	
Safety Approvals	CE, C-Tick, CCC, cULus, TUV gs	
PB-Free	Yes RoHS Compliant	
Dimensions (mm)	60.9 x 31.4 x 38	