

# Full HD 1080P 4 Camera Bullet System

**IQS1080B4**

## IQS1080B4

HD 1080P 4 CAMERA CCTV SYSTEM WITH IR BULLET CAMERAS & 1TB DVR

### DVR FEATURES

- Full HD 1080P Resolution Recording & Playback
- H.264 Video Compression
- 4 Video Input, 2 Video Output
- 4 Audio Input, 1 Audio Output\*
- Compatible with AHD2.0, AHD1.0 and 960H/Analogue Cameras
- HDMI, VGA Outputs
- USB & Internet Backup
- P2P & QR Code Setup
- Remote/Network Access from PC & Mac\*\*

### CAMERA FEATURES

- Full HD 1080P Resolution
- AHD 2.0 Output
- 20m IR Night Vision
- Tamper Resistant
- Wide Angle Lens
- Cable Managed Bracket
- Small, Unobtrusive Design
- Weatherproof (IP66 Rated)
- Easy Installation - Plug and Play

# Features

A Full HD 1080P resolution 4 Camera AHD CCTV kit; supplied ready to fit, complete with a simple to use DVR for viewing, recording and managing the cameras. This complete kit is ideal for anyone looking for a High Definition CCTV system, comprising of 4 Professional Grade External IP66 AHD 1080P bullet cameras and a simple-to-use DVR, the kit is excellent value for money. Included in the package is a IQR1080D4 DVR, which will record and display the cameras in Full 1080P High Definition. The DVR is equipped with HDMI and VGA outputs for easy connection to a TV or Monitor.

## Technical Specifications

### CAMERA - IQC1080B

Brand	IQCCCTV
Model Number	IQC1080B
Style	Bullet Camera
Weather Resistant	Yes (IP66 Rated)
Vandal Resistant	No
Mounting Type	Wall or Ceiling
Dimensions (WHD in mm)	135x55x135
Weight (kg)	0.40
Warranty	1 Year Warranty
Sensor Type	1/2.7" CMOS Megapixel Sensor
DSP Type	IQ 1080P DSP
DSP Functions	Automatic Electronic Shutter Automatic White Balance Automatic Backlight Compensation
Resolution	HD 1080P (AHD 2.0)
Minimum Illumination	0.03 Lux (0 Lux IR On)
Night Vision	20m IR Night Vision
Lens Type	Fixed
Lens Size	3.6mm
Viewing Angle	78°
Operating Voltage	12v DC
Suggested Power Supply	12v DC 1250mA
Video Output	BNC Socket
Audio Output	No
Power Input	DC Socket
RS485 Control	No

### DVR - IQR1080D4

Brand	IQCCCTV
Model Number	IQR1080D4
Camera Inputs	4 CH Inputs
Audio Inputs	1 CH Input
Monitor Outputs	VGA & HDMI Outputs
Spot Output	No
Backup Method	USB & IE
Controls	Mouse, Remote Control, Front Panel
Recording Compression	H.264
Recording Modes	Continuous, Manual, Motion Detection
Recording Rate/Resolution	1920x1080 @ 15fps 1280x720 / 960x576 @ 25fps
Multi-Screen Playback	4
Maximum Recording Capacity	6TB (2TB Included)
Network/Email Alerts	Yes
RS485 Control	Yes
Alarm Inputs/Outputs	No
Dimensions (WxHxD)	300x227x53mm
Weight (Kg)	1.3

All specifications shown are subject to change without notice, please confirm up to date details when ordering. All network specifications and recording times are based upon theoretical scenarios.

Actual performances will vary depending on external factors. No liability will be accepted by Y3K for any errors or omissions in this information. All relevant trade marks acknowledged.  
© Y3K (Europe) Limited 2015

■ DISTRIBUTED BY

