


Professional HD-IP 4MP WDR H265 IR Bullet Camera



X2C4000BP

- 4 Megapixel Resolution
- 3.6mm (78°) Lens
- 20m Smart IR Night Vision
- H265 Video Compression
- PoE Compatible
- Weatherproof (IP66 Rated)



Features

Professional HD-IP IR Bullet Camera, supplied in a rugged IP66 Enclosure with a cable managed bracket which allows for quick, secure installation. A high quality 3.6mm lens for a 78° viewing angle with high power LEDs allowing night vision up to 20 metres.

The 4 Megapixel (2288 x 1712) CMOS Sensor supplied in the X2C4000BP achieves a resolution approximately nine times that of a conventional camera. This makes it possible to cover nine times the monitoring area, the image quality being the same. In addition, when captured images are enlarged the detail is much clearer.

Technical Specifications

X2C4000BP

| | |
|-------------------------------------|---|
| Brand | XVISION |
| Model Number | X2C4000BP |
| Style | HD Bullet Camera |
| Weather Resistant | Yes (IP66 Rated) |
| Vandal Resistant | No |
| Motorised Panning | No |
| Motorised Tilting | No |
| Digital Zoom | No |
| Audio | No |
| Mounting Type | Wall or Ceiling |
| Dimensions (WxHxD) mm | 68x67x196 |
| Weight (kg) | 0.7 |
| Image Sensor | 1/2.9" Sony CMOS |
| Resolution | 4 Megapixel |
| Minimum Illumination | 0.001 Lux |
| Night Vision | 20m |
| Other Features | Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris DNR (Digital Noise Reduction), WDR (Wide Dynamic Range) |
| Lens | 3.6mm |
| Viewing Angle | 78° |
| Video Compression | H265 |
| Video Streams | 1024Kbps-6144Kbps |
| Stream Types | Complex Stream/Video Stream |
| Resolution & Frame Rates | 1228x1712 @25fps |
| Network Connection | RJ45 Socket (10/100 Base-T) |
| WiFi Support | No |
| Network Protocols | TCP/IP, UDP, HTTP, DHCP, RTP/RTSP, DNS, DDNS, NTP, PPPoE, UPNP, SMTP |
| Browser Support | Internet Explorer |
| Mobile Phone Support | Android, iPhone |
| User Authentication | Yes |
| Simultaneous Viewers | 10 |
| Power Over Ethernet | Yes |
| Operating Voltage | 12V DC |
| Power Consumption | <5W |
| Easy Fit | Yes (Optional Ethernet Over Mains Adaptor) |
| Motion Detection | No |
| Presets | No |
| Guard Tours | No |
| Email Alerts | Yes |
| On-Board Recording | No |
| Alarms | No |
| Multi-Camera Software | Yes |

All specifications shown are subject to change without notice, please confirm up-to-date details when ordering. All network specifications and recording times are based upon theoretical scenarios. Actual performances will vary depending on external factors. No liability will be accepted by Y3K for any errors or omissions in this information. All relevant trade marks acknowledged. © Y3K (Europe) Limited 2015

■ DISTRIBUTED BY

