

NEW



100W

Optics

- 2 versions:
1 x 100W warm white COB LED (3200K)
or 1 x 100W cool white COB LED (6000K)
- Manually adjustable beam angle: 12° - 60°
- CRI > 95
- 1.6kHz refresh rate

Control

- DMX channels: 1 or 2 selectable


Dimmer

- 0-100% dimming and variable strobe
- 4 dimming curves in both LED and halogen profiles: Linear, square law, inverse square law and S-curve

Additional features

- 4 push button menu with LCD display
- PowerCON in/out sockets
- 5-Pin XLR in/out sockets
- 3-Pin XLR in/out sockets
- Temperature controlled fan cooling
- Handle on rear panel
- Filter frame and barn doors included

2 YEAR WARRANTY
Valid from date of purchase & subject to Terms & Conditions




Barn Doors included

Order code	Version
ELUM090	100W WW
ELUM091	100W CW

Specifications

- Power consumption: 120W
- Power supply: 100~240V, 50/60Hz
- Dimensions: 430 x 270 x 340mm
- Weight: 7.3kg



150W

Optics

- 2 versions:
1 x 150W warm white COB LED (3200K)
or 1 x 150W cool white COB LED (6000K)
- Manually adjustable beam angle: 12° - 60°
- CRI > 95
- 1.6kHz refresh rate

Control

- DMX channels: 1 or 2 selectable

Dimmer

- 0-100% dimming and variable strobe
- 4 dimming curves in both LED and halogen profiles: Linear, square law, inverse square law and S-curve

Additional features

- 4 push button menu with LCD display
- PowerCON in/out sockets
- 5-Pin XLR in/out sockets
- 3-Pin XLR in/out sockets
- Temperature controlled fan cooling
- Handle on rear panel
- Filter frame and barn doors included

2 YEAR WARRANTY
Valid from date of purchase & subject to Terms & Conditions



Barn Doors included

Order code	Version
ELUM092	150W WW
ELUM093	150W CW

Specifications

- Power consumption: 170W
- Power supply: 100~240V, 50/60Hz
- Dimensions: 430 x 270 x 340mm
- Weight: 7.3kg

