



**Spiral Wrap**  
**T&B Catalog Number:**

SRPE-375-9-C

**UPC Number:**

72849410780

**Status:**

Active

**Description:**

Spiral Wrap, Natural Polyethylene for Temperatures up to 50 Degrees Celsius (122 F), Outside Diameter of 9.53mm (0.375 Inches), Pitch of 11.13mm (0.438 Inches), Nominal Wall Thickness of 1.32mm (0.052 Inches), 30.48m Reel (100 Feet)

**Features**

Perfect for protection of bundles from .062 to 7 inch diameters.

Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation, and rigidity.

Available in three material types.

**General**

Style	Reverse Cut
Material	Polyethylene
Color	Natural

**Dimension Information**

Pitch (inches)	0.438
Nominal Wall Thickness (inches)	0.052
Max. Wire Bundle Diameter (inches)	3.000
Min. Wire Bundle Diameter (inches)	0.313
Outside Diameter (inches)	0.375

**Specifications**

Flammability Rating	UL 94 HB
---------------------	----------

**Tooling**

Application Tools	SR-100
-------------------	--------

**Packaging**

T&B Order Multiple	1
T&B Inner Pack	1
Package in Units	6
Feet per Roll	100
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. Each

**Notes**

Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation and rigidity.

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321

