



TE CONNECTIVITY (TE)

- 44AM1121-16-9/96-9CS2275
- TE Internal Number: 138517-000
- Mil-Spec: M27500-16ML2T08
- Alias ID: 4-1191004-8

Always EU RoHS/ELV Compliant

Product Type Features *Cable Type* Spec 44

- Shielded **Yes**
- Cable Style **Round Braided Shielded & Jacketed**
- Product Type **Cable**
- Product Classification **High Performance - Spec 44, 55 & RCW**

Configuration Features

Number of Strands 19

- Number of Conductors 2

Electrical Characteristics -- Voltage Rating (V) 600

Body Features

- Shield Material **Tin-Plated Copper**
- Jacket Color **White**
- Wire Color **White with Blue Stripe, White**
- Conductor Material **Tin-Plated Copper**
- Shield Size (AWG) **38**

Dimensions

- Strand Size (AWG) **29**
- Overall Outside Diameter **4.55 mm [.179 in]**
- Wire Size (AWG) **16**
- Wire Diameter **1.83 mm [.072 in]**

Usage Conditions -- Operating Temperature Range (°C) -65 – 150